

EPIC® POWERLOCK A6 C

EPIC®POWERLOCK

660A

240mm²



가

ex)

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

EPIC® POWERLOCK A6 C

가
가

ETIM 5:

ETIM 5.0 Class-ID: EC000437

ETIM 5.0 class :

ETIM 6:

ETIM 6.0 Class-ID: EC000437

ETIM 6.0 Class-Description: Housing for industrial connectors

(V):

1000V

:

8 kV

(A):

. 660 A

:

3

:

Crimp termination:

/ :

1

:

: 35 - 240 mm²

:

: PBT

: PA

가:

IP 67 (,)

IP 20 ()

:

500

VDE- :

VDE D42

:

-25°C ~+125°C

가 VAT 가 가 .

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



EPIC® POWERLOCK A6 C

	Article description		
44420226	POWERLOCK A6 PE/GN	Ø 5.5 mm (4x)	PE,
44420227	POWERLOCK A6 N/BL	Ø 5.5 mm (4x)	N,
44420228	POWERLOCK A6 L1/BN	Ø 5.5 mm (4x)	L1,
44420229	POWERLOCK A6 L2/BK	Ø 5.5 mm (4x)	L2,
44420230	POWERLOCK A6 L3/GY	Ø 5.5 mm (4x)	L3,
L2/	L1/		
44420317	POWERLOCK A6 L1/RD	Ø 5.5 mm (4x)	L1,

EPIC® POWERLOCK A6 C



(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16