

EPIC® POWERLOCK Crimp contacts

EPIC® POWERLOCK 660A 35mm² ~ 240mm² 가

660 A
(400 A)



ETIM 5:

ETIM 5.0 Class-ID: EC000796
ETIM 5.0 class :

가 VAT 가 가 .

(23.04.2024)



EPIC® POWERLOCK Crimp contacts

		Version	Crimp sunk	PU
44420260	POWERLOCK SP M12	가 , M12	-	1
- A6 C				
44420261	POWERLOCK QP M12	M12 ,	-	1
44420293	POWERLOCK SCM 35	35 mm ²	35	1
44420294	POWERLOCK SCM 50	50 mm ²	50	1
44420295	POWERLOCK SCM 70	70 mm ²	70	1
44420231	POWERLOCK SCM 95	95 mm ²	95	1
44420233	POWERLOCK SCM 120	120 mm ²	120	1
44420256	POWERLOCK SCM 150	150 mm ²	150	1
44420234	POWERLOCK SCM 185	185 mm ²	185	1
44420339	POWERLOCK SCM 240 NEW	240 mm ²	240	1
44420290	POWERLOCK QCM 35	35 mm ²	35	1
44420291	POWERLOCK QCM 50	50 mm ²	50	1
44420292	POWERLOCK QCM 70	70 mm ²	70	1
44420236	POWERLOCK QCM 95	95 mm ²	95	1
44420238	POWERLOCK QCM 120	120 mm ²	120	1
44420257	POWERLOCK QCM 150	150 mm ²	150	1
44420239	POWERLOCK QCM 185	185 mm ²	185	1
44420324	POWERLOCK QCM 240 NEW	240 mm ²	240	1

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

EPIC® POWERLOCK Crimp contacts



(23.04.2024)

©2024 Lapp Group - all rights reserved.
<http://lappkorea.lappgroup.com>
data sheet

PN 0456 / 02_03.16