


EPIC® SIGNAL M17 A3

EPIC® M17 SIGNAL ,

310° 가

Made in Germany



/ ac
EMC

/

ETIM 5:

ETIM 5.0 Class-ID: EC002635

ETIM 5.0 class : ()

(21.02.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

EPIC® SIGNAL M17 A3

ETIM 6:

(V):

:

(A):

:

:

/ :

:

:

가:

:

:

ETIM 6.0 Class-ID: EC002635

ETIM 6.0 Class : ()

IEC: 48 V AC, 74 V DC

1.5 kV

3.6 A

3

: 8(1mm), 17(0.6mm)

: 0.06 - 0.56mm² (0,6mm)

: 0.06 - 1.0 mm² (1mm)

:

: PA,

: FPM

IP 67

100

-40°C +125°C

가 VAT 가 가 .

(21.02.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



EPIC® SIGNAL M17 A3

	Article description			/ PU
M17 A3, ,				
44423114	EPIC® M17	Ø 2.7 mm (4x)	8	5
44423112	EPIC® M17	Ø 2.7 mm (4x)	8	5
44423115	EPIC® M17	Ø 2.7 mm (4x)	17	5
44423113	EPIC® M17	Ø 2.7 mm (4x)	17	5