


EPIC® SIGNAL M23 12

M23

EPIC® SIGNAL M23 M23

12

Made in Germany



M23

가 가 .

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

EPIC® SIGNAL M23 12

ETIM 5:

ETIM 5.0 Class-ID: EC000438

ETIM 5.0 class :

ETIM 6:

ETIM 6.0 Class-ID: EC000438

ETIM 6.0 Class-Description: Contact insert for industrial connectors

(V):

IEC 61984 : 100V

:

1.5 kV

(A):

7 A

:

3

:

< 4 mOhm

:

/ :

12

12*1mm contacts

:

: 0.14 - 1.0 mm²

: 1.0 mm²

:

100

VDE-

:

: VDE-REG.

C24(EN 61984

, DIN

VDE 0100-410 SELV가

)

UL : E249137

:

-25°C ~+125°C

. P- ' = (), E- = (P-) , E- , P-

가 VAT 가 가 .

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet



PN 0456 / 02_03.16



EPIC® SIGNAL M23 12

	Article description				/ PU
12-	, P- = ()				
73002712	P-		-	12	5
73002713	P-		-	12	20
73002714	P-	+	,	12	5
73002715	P-	+	,	12	20
73002716	P-	+	,	12	5
73002717	P-	+	,	12	20
12-	, E- = ()				
73002718	E-Part		-	12	5
73002719	E-Part		-	12	20
73002720	E-Part	+	,	12	5
73002721	E-Part	+	,	12	20
73002722	E-Part	+	,	12	5
73002723	E-Part	+	,	12	20

EPIC® SIGNAL M23 12



(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16