

EPIC® H-Q 5 PE

Protection earth contacts for EPIC® H-Q 5 und H-Q 7 series

Crimpable and thus vibration-proof PE protective conductor contact for rectangular connector inserts EPIC® H-Q 5 and EPIC® H-Q 7.

정보

Crimpable PE protective conductor contact for inserts EPIC® H-Q and EPIC® H-Q 7.



Lapp의 보완 자동화 요소



식음료



기계 및 플랜트 엔지니어링



철도



풍력 에너지



옥외용에 적합



최적 변형 방지



튼튼함

응용 범위

For use with EPIC® H-Q 5 and EPIC® H-Q 7 rectangular connector inserts.

최근 업데이트 (23.12.2023)

©2023 Lapp Group - all rights reserved.

제품 관리 <http://lappkorea.lappgroup.com>

해당하는 data sheet 에서 최근 자료를 찾을 수 있습니다.

PN 0456 / 02_03.16

EPIC® H-Q 5 PE

제품 특성

Crimp connection creates a vibration-proof connection, ensures maximum contacting reliability between contact and cable and is suitable for automated assembly.

Silver coating with tarnish protection for high electrical conductivity and thermal conductivity.

Suitable for conductor cross-sections up to 4.0 mm².

기술 데이터

분류 ETIM 5:

ETIM 5.0 Class-ID: EC000796

ETIM 5.0 class 설명: 산업용 커넥터 콘택트

분류 ETIM 6:

ETIM 6.0 Class-ID: EC000796

ETIM 6.0 Class-Description: Contact for industrial connectors

접촉 저항:

< 2 mOhm

체결 방법:

Crimp termination: 0.75 mm² ... 4.0 mm²

재료:

brass silver plated CuZn / Ag

기계적작업 사이클:

500

비고

사진은 각각의 제품 상세 이미지를 대변하지는 않습니다.

가격은 VAT 및 할증료가 없는 가격. 비즈니스 고객에게만 판매

EPIC® H-Q 5 PE

품번	Article description	Version	단면적 (최소) (mm ²)	단면적 (최대) in mm ²	스트리핑 길이 (mm)	피스 / PU
10431605	EPIC® H-Q 5 PE SCEM 0.75 ... 1.0 mm ²	메일	0.75	1	7.4	10
10431615	EPIC® H-Q 5 PE SCEM 1.5 mm ²	메일	1.5	1.5	7.4	10
10431625	EPIC® H-Q 5 PE SCEM 2.5 mm ²	메일	2.5	2.5	7.4	10
10431640	EPIC® H-Q 5 PE SCEM 4.0 mm ²	메일	4	4	7.4	10
10432605	EPIC® H-Q 5 PE BCEM 0.75 ... 1.0 mm ²	피메일	0.75	1	7.4	10
10432615	EPIC® H-Q 5 PE BCEM 1.5 mm ²	피메일	1.5	1.5	7.4	10
10432625	EPIC® H-Q 5 PE SCEM 2.5 mm ²	피메일	2.5	2.5	7.4	10
10432640	EPIC® H-Q 5 PE BCEM 4.0 mm ²	피메일	4	4	7.4	10

EPIC® H-Q 5 PE