



**EPIC® H-A 32 SGRL**

2 ( ),

2 2

2 H-A 32



H-A, H-D STA

M40 housing extension on M50 with SKINTOP 53112083 possible (clamping range 27 - 35 mm)

# EPIC® H-A 32 SGRL

ETIM 5:

ETIM 5.0 Class-ID: EC000437

ETIM 5.0 class :

ETIM 6:

ETIM 6.0 Class-ID: EC000437

ETIM 6.0 Class-Description: Housing for industrial connectors

:

:

: -  
: NBR

가:

IP 65 (latched)

:

-40°C to +100°C, short-term up to +125°C

가 VAT 가 가 .

(16.07.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16



# EPIC® H-A 32 SGRL

	Article description	M	PG	Neck	Packaging unit
H-A	: - (2 , )				
10482000	H-A 32 SGRL 21	-	21	yes	5
19482100	H-A 32 SGRL M32 ZW	32	-	yes	5
79506800	H-A 32 SGRL M40	40	-	-	5

(16.07.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16