

EPIC® ULTRA H-A 3 Housing

(EMC)

EPIC® H-A 3

EMC

UL50E



Space-saving due to compact dimensions.

, - 360° 가

EMC-

(. ,)

IEC 68-2-52, 2 , NSS, 480
DIN EN ISO 9227 ,
DIN EN 6988 -
EMC : 53112630

ETIM 5:

ETIM 5.0 Class-ID: EC000437

ETIM 5.0 class :

:

:

:

: NBR

가:

IP 65

NEMA 250, UL50E: 12, 4, 4X (latched)

VDE- :

: VDE-REG. : B437

UL- :

UL : E75770

:

-40°C to +100°C, short-term up to +125°C

(24.04.2024)



EPIC® ULTRA H-A 3 Housing

가 VAT 가 가 .

(24.04.2024)



EPIC® ULTRA H-A 3 Housing

Article number	Article description	Screening diameter (min)		M	/ PU
Hood					
10423300	EPIC® ULTRA H-A 3 TG	-	-	20	10
10423600	EPIC® ULTRA H-A 3 TGV 5-9 BRUSH	3	5.0 - 9.0	-	10
10423620	EPIC® ULTRA H-A 3 TGHV 6-13 BRUSH	6	6.0 - 13.0	-	10
10423201	EPIC® ULTRA H-A 3 TS	-	-	20	10
10423650	EPIC® ULTRA H-A 3 TSV 5-9 BRUSH	3	5.0 - 9.0	-	10
Cable coupler hood					
10423204	EPIC® ULTRA H-A 3 TBF	-	-	20	10
Panel-mount base					
10423200	EPIC® ULTRA H-A 3 AG	-	-	-	10
10423202	ULTRA H-A 3 AGS	-	-	-	10
10423203	EPIC® ULTRA H-A 3 AGSV open	-	-	20	10
Surface-mount base					
19512702	ULTRA H-A 3 AGSV	-	-	20	10
10423640	EPIC ULTRA H-A 3 EGS M20	-	-	20	10

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16