

EPIC® H-B 24 TG

H-B.

UL50E



Lapp



M40 housing extension on M50 with SKINTOP 53112083 possible (clamping range 27 - 35 mm)

(22.07.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



EPIC® H-B 24 TG

, low

neck /

ETIM 5:

ETIM 5.0 Class-ID: EC000437

ETIM 5.0 class :

ETIM 6:

ETIM 6.0 Class-ID: EC000437

ETIM 6.0 Class-Description: Housing for industrial connectors

:

: - ,

: -

: NBR

가:

IP 65 (latched)

NEMA 250, UL50E: 12, 4 (latched)

VDE- :

: VDE-REG. : B437

UL- :

UL : E75770

:

-40°C to +100°C, short-term up to +125°C

가 VAT 가 가 .

(22.07.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



EPIC® H-B 24 TG

	Article description	M	PG	Neck	Packaging unit
H-B	: (,)				
10121000	H-B 24 TG 21	-	21	yes	5
10111000	H-B 24 TG 29	-	29	yes	5
19121000	H-B 24 TG M25	25	-	-	5
19111000	H-B 24 TG M32	32	-	-	5
19111500	H-B 24 TG M40	40	-	-	5