



EPIC® H-B 32 SGRL

H-B 2

2 2 가



M40 housing extension on M50 with SKINTOP 53112083 possible (clamping range 27 - 35 mm)

2

ETIM 5:

ETIM 5.0 Class-ID: EC000437

ETIM 5.0 class :

ETIM 6:

ETIM 6.0 Class-ID: EC000437

ETIM 6.0 Class-Description: Housing for industrial connectors

:

:

: NBR

가:

IP 65 (latched)

:

-40°C to +100°C, short-term up to +125°C

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



EPIC® H-B 32 SGRL

가 VAT 가 가 .

(24.04.2024)



EPIC® H-B 32 SGRL

	Article description	M	PG	/ PU
H-B	: - (2 ,)			
10138000	H-B 32 SGRL 29	-	29	5
19138000	H-B 32 SGRL M32	32	-	5
19145400	H-B 32 SGRL M40	40	-	5

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16