

EPIC® H-BE 10 Push-In termination

EPIC H-BE

- : , - 가



CE UK CA



Lapp



가

(21.08.2024)

EPIC® H-BE 10 Push-In termination

2mm

-

가

Railway applications

- Fire protection on railway vehicles: Test according EN 45545-2. Requirement sets R22 and R23. Hazard level HL1, HL2 and HL3

EPIC® H-BE

/

ETIM 5:

ETIM 5.0 Class-ID: EC000438

ETIM 5.0 class :

ETIM 6:

ETIM 6.0 Class-ID: EC000438

ETIM 6.0 Class-Description: Contact insert for industrial connectors

(V):

IEC: 500 VUL: 600 VCSA: 600 V

:

6 kV

(A):

IEC: 16 A

UL: 13 A

CSA: 13 A

:

3

:

UL94 V-0

:

< 2 mOhm

:

/ :

10 + PE

:

- : 0.14 - 2.5mm²

(mm):

10

:

PA

:

500

:

UL-

:

UL

: E75770

:

-40°C to +100°C, short-term up to +125°C

가

VAT

가

가

.

(21.08.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



EPIC® H-BE 10 Push-In termination

	Article description	Contact type			Packaging unit
H-BE 10 Push-In termination					
44423202	EPIC® H-BE 10 SP		yes	1 - 10	10
44423203	EPIC® H-BE 10 BP		yes	1 - 10	10


(21.08.2024)

©2024 Lapp Group - all rights reserved.
<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

EPIC® H-BE 10 Push-In termination



(21.08.2024)

©2024 Lapp Group - all rights reserved.
<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16