




EPIC® H-BE 48 Crimp termination

4 mm²

가



Lapp



가

EPIC® H-BE

Railway applications

- Fire protection on railway vehicles: Test according EN 45545-2. Requirement sets R22 and R23. Hazard level HL1, HL2 and HL3

(01.05.2024)

EPIC® H-BE 48 Crimp termination

/	
ETIM 5:	ETIM 5.0 Class-ID: EC000438 ETIM 5.0 class :
ETIM 6:	ETIM 6.0 Class-ID: EC000438 ETIM 6.0 Class-Description: Contact insert for industrial connectors
(V):	IEC: 500 VUL: 600 VCSA: 600 V
:	6 kV
(A):	IEC: 16 A UL: 16 A CSA: 16 A
:	3
:	UL94 V-0
:	< 2 mOhm
:	, /
/ :	48 + PE
:	: 0.14 ~ 4.0 mm ²
:	PC,
:	500
:	UL- :
:	UL : E75770
:	-40°C ... +125°C

가 VAT 가 가 .



EPIC® H-BE 48 Crimp termination

	Article description	Contact type		/ PU
10186202	EPIC® H-BE 24 SCM 25-48		25 - 48	5
10187202	EPIC® H-BE 24 BCM 25-48		25 - 48	5

(01.05.2024)

©2024 Lapp Group - all rights reserved.
<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16