



EPIC® H-EE 10


H-BE

가 H-EE


가



M



F



가

H-EE

H-B

()

ETIM 5:

ETIM 5.0 Class-ID: EC000438
ETIM 5.0 class :

ETIM 6:

ETIM 6.0 Class-ID: EC000438
ETIM 6.0 Class-Description: Contact insert for industrial connectors

(V):

IEC: 500 VUL: 600 VCSA: 600 V

:

6 kV

(A):

IEC: 16 A

(24.04.2024)

EPIC® H-EE 10

	UL: 16 A
	CSA: 16 A
	3
	< 2 mOhm
	, /
	10 + PE
	: 0.5 - 4.0 mm ²
	100
VDE-	UL-
	UL : E75770
	-40°C to +100°C, short-term up to +125°C

가 VAT 가 가 .



EPIC® H-EE 10

	Article description	Contact type			/ PU
H-EE 10					
10180400	H-EE 10 SC		machined	1 - 10	10
10181400	H-EE 10 BC		machined	1 - 10	10

(24.04.2024)


©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

EPIC® H-EE 10



(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16