

EPIC® H-Q 12

H-A 3

EPIC® H-Q 12 H-A 3

12

Made in Europe



Lapp



Mateable with market standard connectors.
Suitable for conductor cross-sections from 0.14 - 4.0 mm².

PE

ETIM 5:

ETIM 5.0 Class-ID: EC000438

ETIM 5.0 class :

(01.08.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

EPIC® H-Q 12

ETIM 6:

(V):

:

(A):

:

:

:

:

/ :

:

:

:

VDE-

:

:

ETIM 6.0 Class-ID: EC000438

ETIM 6.0 Class-Description: Contact insert for industrial connectors

IEC: 400 V

UL: 600 V

CSA: 600 V

6 kV

IEC: 10 A

UL: 14 A

CSA: 10 A

3

UL94 V-0

< 3 mOhm

, /

12 + PE

: 0.14 - 2.5 mm²

PA

200

CSA :

CSA : 262771

UL- :

UL : E75770

-40°C ~ +120°C

가 VAT

가 가 .

(01.08.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



EPIC® H-Q 12

	Article description	Contact type		Packaging unit
H-Q 12 Crimp termination				
44424049	H-Q 12 SC		1 - 12	10
44424050	H-Q 12 BC		1 - 12	10

(01.08.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16