

EPIC® H-Q 7 PE-C

Connector insert with 7 contacts and protection earth crimping contact

Compact, 7-pole rectangular connector insert, powerful up to 10 A, for crimpable PE contact.

Made in Germany



Lapp



Compact contact arrangement allows 7 contacts + 1 PE contact in a small installation space.

Crimp connection creates a vibration-proof connection, ensures maximum contacting reliability between contact and cable and is suitable for automated assembly.

(05.08.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

EPIC® H-Q 7 PE-C

Special PE crimp contact enables automated assembly of a completely vibration-proof connector.
 Mateable with market standard connectors.
 Suitable for conductor cross-sections from 0.14 - 2.50 mm².

For power supply connection of devices and machines in various applications.
 Suitable for wiring inside the control cabinet.
 Can be used with many EPIC® rectangular connector housings.

ETIM 5:	ETIM 5.0 Class-ID: EC000438
	ETIM 5.0 class :
ETIM 6:	ETIM 6.0 Class-ID: EC000438
	ETIM 5.0 class :
(V):	400 V
:	6 kV
(A):	10 A
:	3
:	UL94 V-0
:	< 2 mOhm
/ :	7 + PE
:	: 0.14 - 2.5 mm ²
	Crimp termination PE: 0.75 mm ² ... 4.0 mm ²
:	
:	500
VDE- :	UL- :
	UL : E75770
:	-40°C ~ +120°C

가 VAT 가 가 .



EPIC® H-Q 7 PE-C

	Article description	Contact type		Packaging unit
10431710	EPIC H-Q 7 SCM PE-C		7	10
10432710	EPIC H-Q 7 BCM PE-C		7	10

(05.08.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

EPIC® H-Q 7 PE-C



(05.08.2024)