

# EPIC® H-Q 12

H-A 3

EPIC® H-Q 12      H-A 3

12

Made in Europe



Lapp



Mateable with market standard connectors.  
Suitable for conductor cross-sections from 0.14 - 4.0 mm<sup>2</sup>.

PE

ETIM 5:

ETIM 5.0 Class-ID: EC000438  
ETIM 5.0 class :

(22.07.2024)

# EPIC® H-Q 12

ETIM 6:

ETIM 6.0 Class-ID: EC000438

ETIM 6.0 Class-Description: Contact insert for industrial connectors

(V):

IEC: 400 V  
UL: 600 V  
CSA: 600 V

:

6 kV

(A):

IEC: 10 A  
UL: 14 A  
CSA: 10 A

:

3

:

UL94 V-0

:

< 3 mOhm

:

, /

/ :

12 + PE

:

: 0.14 - 2.5 mm<sup>2</sup>

:

PA

:

200

VDE-

:

CSA :

CSA : 262771

UL- :

UL : E75770

:

-40°C ~ +120°C

가 VAT 가 가 .

(22.07.2024)



## EPIC® H-Q 12

	Article description	Contact type		Packaging unit
H-Q 12 Crimp termination				
44424049	H-Q 12 SC		1 - 12	10
44424050	H-Q 12 BC		1 - 12	10

(22.07.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16