

EPIC® H-Q 7 PE-C

Connector insert with 7 contacts and protection earth crimping contact

Compact, 7-pole rectangular connector insert, powerful up to 10 A, for crimpable PE contact.

Made in Germany



Lapp



Compact contact arrangement allows 7 contacts + 1 PE contact in a small installation space.

Crimp connection creates a vibration-proof connection, ensures maximum contacting reliability between contact and cable and is suitable for automated assembly.

(20.07.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

EPIC® H-Q 7 PE-C

Special PE crimp contact enables automated assembly of a completely vibration-proof connector.
 Mateable with market standard connectors.
 Suitable for conductor cross-sections from 0.14 - 2.50 mm².

For power supply connection of devices and machines in various applications.
 Suitable for wiring inside the control cabinet.
 Can be used with many EPIC® rectangular connector housings.

| | |
|---------|--|
| ETIM 5: | ETIM 5.0 Class-ID: EC000438 |
| | ETIM 5.0 class : |
| ETIM 6: | ETIM 6.0 Class-ID: EC000438 |
| | ETIM 5.0 class : |
| (V): | 400 V |
| : | 6 kV |
| (A): | 10 A |
| : | 3 |
| : | UL94 V-0 |
| : | < 2 mOhm |
| / : | 7 + PE |
| : | : 0.14 - 2.5 mm ² |
| | Crimp termination PE: 0.75 mm ² ... 4.0 mm ² |
| : | |
| : | 500 |
| VDE- : | UL- : |
| | UL : E75770 |
| : | -40°C ~ +120°C |

가 VAT 가 가 .



EPIC® H-Q 7 PE-C

| | Article description | Contact type | | Packaging unit |
|----------|---------------------|--------------|---|----------------|
| 10431710 | EPIC H-Q 7 SCM PE-C | | 7 | 10 |
| 10432710 | EPIC H-Q 7 BCM PE-C | | 7 | 10 |

(20.07.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

EPIC® H-Q 7 PE-C



(20.07.2024)