

EPIC® H-Q 7 PE-S

Connector insert with 7 crimping contacts and protection earth screwing contact

Compact, 7-pole rectangular connector insert, powerful up to 10 A, with screwable PE contact.

Made in Germany



Lapp



Compact contact arrangement allows 7 contacts + 1 PE contact in a small installation space.

Crimp connection creates a vibration-proof connection, ensures maximum contacting reliability between contact and cable and is suitable for automated assembly.

(22.07.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

EPIC® H-Q 7 PE-S

Protective earth (PE) can be connected in two ways: Variant "PE-S" can be used with a PE screw contact, variant "PE-C" with a PE crimp contact.

Mateable with market standard connectors.

Suitable for conductor cross-sections from 0.14 - 2.50 mm².

For power supply connection of devices and machines in various applications.

Suitable for wiring inside the control cabinet.

Can be used with many EPIC® rectangular connector housings.

ETIM 5:	ETIM 5.0 Class-ID: EC000438
	ETIM 5.0 class :
ETIM 6:	ETIM 5.0 Class-ID: EC000438
	ETIM 6.0 Class-Description: Contact insert for industrial connectors
(V):	400 V
:	6 kV
(A):	10 A
:	3
:	UL94 V-0
:	< 2 mOhm
/ :	7 + PE
:	: 0.14 - 2.5 mm ²
	Screw termination PE: 0.25 mm ² ... 4.0 mm ²
:	
:	500
VDE- :	UL- :
	UL : E75770
:	-40°C ~ +120°C

가 VAT 가 가 .

(22.07.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



EPIC® H-Q 7 PE-S

	Article description	Contact type		Packaging unit
10431700	EPIC H-Q 7 SCM PE-S		7	10
10432700	EPIC H-Q 7 BCM PE-S		7	10

(22.07.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

EPIC® H-Q 7 PE-S



(22.07.2024)

©2024 Lapp Group - all rights reserved.
<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16