

EPIC® MH 4.0mm Contacts

Machined EPIC® MH 4.0 contacts are suitable for the safe transmission of larger currents. The silver coating ensures low contact resistance and thus little loss and less heat generation.

High quality contact with 4mm pin diameter for a safe transmission of larger currents



Lapp



High quality contact with 4mm pin diameter for a safe transmission of larger currents
For cross section from 1,5mm² up to 10mm² available

Crimp connection for permanent vibration proof contacting
With the appropriate tools, good contacting is created quickly and easily

/

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

EPIC® MH 4.0mm Contacts

ETIM 5:

ETIM 5.0 Class-ID: EC000796

ETIM 5.0 class :

ETIM 6:

ETIM 6.0 Class-ID: EC000796

ETIM 6.0 Class-Description: Contact for industrial connectors

:

< 5 mOhm

:

: 1.5 ~ 10 mm²

(mm):

10

:

500

가 VAT 가 가 .

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



EPIC® MH 4.0mm Contacts

	Article description	Contact type	(mm ²)	/ PU
44423250	EPIC® MH SCEM AG 1.5sqmm D=4.0		1.5	100
44423255	EPIC® MH BCEM AG 1.5sqmm D=4.0		1.5	100
44423251	EPIC® MH SCEM AG 2.5sqmm D=4.0		2.5	100
44423256	EPIC® MH BCEM AG 2.5sqmm D=4.0		2.5	100
44423252	EPIC® MH SCEM AG 4sqmm D=4.0		4	100
44423257	EPIC® MH BCEM AG 4sqmm D=4.0		4	100
44423253	EPIC® MH SCEM AG 6sqmm D=4.0		6	100
44423258	EPIC® MH BCEM AG 6sqmm D=4.0		6	100
44423254	EPIC® MH SCEM AG 10sqmm D=4.0		10	100
44423259	EPIC® MH BCEM AG 10sqmm D=4.0		10	100