


EPIC® MH 36

High flexibility by the use of any combination of modules in one connector

가
가

가
36



Lapp



가 36
Crimp connection for permanent vibration proof contacting
EPIC® MH 가

1
Railway applications

- Fire protection on railway vehicles: Test according EN 45545-2. Requirement sets R22 and R23. Hazard level HL1, HL2 and HL3

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

EPIC® MH 36

/

ETIM 5:

ETIM 5.0 Class-ID: EC002641

ETIM 5.0 : ()

ETIM 6:

ETIM 6.0 Class-ID: EC002641

ETIM 6.0 Class : ()

(V):

250 V

:

4 kV

(A):

10 A

:

3

:

UL94 V-0

:

< 5 mOhm

/ :

36

:

: 0.14 - 2.5 mm²

:

,

:

500

:

UL- :

UL : E75770

:

-40°C +125°C

가 VAT 가 가 .

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



EPIC® MH 36

	Article description	Contact type		Slots	/ PU
44423266	EPIC® MHS 36 CM		36	2	10
44423267	EPIC® MHB 36 CM		36	2	10

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16