

EPIC® ULTRA H-B 16 TGH QB

(EMC)

EPIC® EMC , , UL50E, Nema250

EMC

Made in Germany



(23.08.2024)



EPIC® ULTRA H-B 16 TGH QB

, - 360°
가

EMC- (. ,)

BRUSH 가, BRUSH
DIN EN 6988 -
IEC 68-2-52, 2
DIN EN ISO 9227 , NSS, 480

| | |
|---------|---|
| ETIM 5: | ETIM 5.0 Class-ID: EC000437 |
| | ETIM 5.0 class : |
| ETIM 6: | ETIM 6.0 Class-ID: EC000437 |
| | ETIM 6.0 Class-Description: Housing for industrial connectors |
| : | : - - |
| | : |
| | : NBR |
| | : |
| | : PA |
| | : |
| 가: | IP 67 |
| | NEMA 250, UL50E: 12, 4, 4X (latched) |
| : | -40°C ~ +100°C |

가 VAT 가 가 .

(23.08.2024)



EPIC® ULTRA H-B 16 TGH QB

| | Article description | Clamping range in mm | (mm) Ø , | / PU |
|----------|---|----------------------|----------|------|
| H-B | : | (| , |) |
| 70250274 | EPIC ULTRA H-B 16 TGH QB 15-23 | 15.0 - 23.0 | - | 1 |
| 70250275 | EPIC ULTRA H-B 16 TGH QB 15-23 BRUSH | 15.0 - 23.0 | 7 | 1 |
| 70250276 | EPIC ULTRA H-B 16 TGH QB 19-28 | 19.0 - 28.0 | - | 1 |
| 70250261 | EPIC ULTRA H-B 16 TGH QB 19-28 BRUSH | 19.0 - 28.0 | 7 | 1 |

(23.08.2024)

©2024 Lapp Group - all rights reserved.
<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16