

EPIC® SOLAR 4 GEN2 M

Always a good sign! Our weather-resistant solar connectors for cabling solar modules up to 1500 V are TÜV SÜD certified. The connector with the self-retaining cap nut and haptic feedback is compatible with many connectors from well-known manufacturers. Connector assembly can also be carried out fully automatically.

1.5kV



Extremely weatherproof and durable thanks to the high-quality materials and solid construction.
Compatible with other systems in the industry.
Ideal for fully automated connector assembly.
Self-retaining cap nut and contacting with haptic feedback simplify assembly and provide protection from tampering.
Double snap-in hooks secure the crimp contact to the connector.
Low contact resistance at the contact point between the connector and socket for efficient energy transmission.
Suitable for conductor cross-sections of up to 6 mm² for overcoming long cable distances.

With the TÜV SÜD testing mark.

Articles available with or without contacts. Articles without contacts available in different packaging units.

For the cabling of solar modules, inverters and stand-alone systems.
For modern, high-performance photovoltaic systems up to 1500 V.
For use with EPIC® SOLAR 4 GEN2 F mating connectors (socket insert).

Can be used with many ÖLFLEX® solar cables.

Plugged connections have protection class IP 68 (1 m for 1 h).

:

PA

가 VAT 가 가 .

(22.06.2024)



EPIC® SOLAR 4 GEN2 M

	Clamping range min	Clamping range max	Clamping range in mm	PL_VERPACKUNGSEINHEIT1
381166810	-	-	-	-
44428277	5.2	7	5.2 - 7.0	100
381166461	5.2	7	5.2 - 7.0	700
44428270	5.2	7	5.2 - 7.0	100

(22.06.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16