



# EPIC® SOLAR 4Plus Set

EPIC® SOLAR 4Plus M

4 mm , 가  
10  
Made in Germany



(24.04.2024)



# EPIC® SOLAR 4Plus Set

Suitable for various ÖLFLEX® SOLAR cables

NEC

TUEV tested according IEC 62852: Connectors for DC-application in photovoltaic systems

(Solartracker)

10  
4 mm 가  
1,500 V

TUEV Rheinland certificate no.:  
R 60134622

(V):	1.5 kV
:	16 kV
:	3
:	UL94 V-0
:	< 0.5 mOhm
:	PA
가:	IP68 (10h/1m)
:	100
:	II
:	-40°C ... +105°C

가 VAT 가 가 .

(24.04.2024)



# EPIC® SOLAR 4Plus Set

		Cross-section (mm <sup>2</sup> )	Clamping range in mm	(A)	PU
EPIC® SOLAR 4Plus Set, 가 가 , 10 ,					
44428255	EPIC® SOLAR 4Plus M+F 4mm <sup>2</sup> ... 6mm <sup>2</sup> Set	4.0 - 6.0	5.2 - 7.1	30	1

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16