


FLEXIMARK® Collar closed

FLEXIMARK® Collar

가



가

, , (, , , ...)

Extremely flame-retardant according to
UL 94 V0

LMB

(collar)

ETIM 5:	ETIM 5.0 Class-ID: EC002248
	ETIM 5.0 Class :
ETIM 6:	ETIM 6.0 Class-ID: EC002248
	ETIM 6.0 Class :
:	Transparent
:	PVC
:	-40°C +80°C

FLEXIMARK® Collar closed

가	VAT	가	가	.	.	) LCK 32	640	640	1	PU
FLEXIMARK®										

FLEXIMARK® Collar closed

		(mm)	Ø (mm)	PU	PU
FLEXIMARK® Collar closed					
83290211	FLEXIMARK® collar halogen-free 2-4/10 TR	10	2.0 - 4.0	1000	1
83290212	FLEXIMARK® collar halogen-free 2-4/15 TR	15	2.0 - 4.0	1000	1
83252693	FLEXIMARK® collar halogenfree 1,4-5/23 TR	23	1.4 - 5.0	500	1
83290213	FLEXIMARK® collar halogen-free 2-4/30 TR	30	2.0 - 4.0	500	1
83290214	FLEXIMARK® collar halogen-free 4-7/10 TR	10	4.0 - 7.0	500	1
83290215	FLEXIMARK® collar halogen-free 4-7/15 TR	15	4.0 - 7.0	500	1
83252694	FLEXIMARK® collar halogen-free 5-11/23 TR	23	5.0 - 11.0	200	1
83252675	FLEXIMARK® collar halogen-free 5-11/30 TR	30	5.0 - 11.0	200	1