

# FLEXIMARK®

FLEXIMARK® Organized Shrink Tube



가

: UL 224

Easy to print via FLEXIMARK®  
software Flexisoft and FLEXIMARK®

thermal transfer printer SQUIX, EOS5 or EOS2  
: FTI-X 60-300 BK( : 83260206)

(23.04.2024)

**FLEXIMARK®**

ETIM 5:

ETIM 5.0 Class-ID: EC001288

ETIM 5.0 class :

ETIM 6:

ETIM 6.0 Class-ID: EC001288

ETIM 6.0 Class :

:

SNCF-NF F00-608  
가

:

가

가

:

: 2:1

: 3:1

:

Halogen-free version:

-55°C to +105°C

Not halogen-free Version:

-55°C to +135°C

: +90°C

가 VAT  
FLEXIMARK®

가 가 .

. ) LCK 32

640

640

1

PU



FLEXIMARK®

			(mm)	(mm)	PU	PU
83260225	FLEXIMARK® O.shr 2.4/1.2-12.5 YE		1.2 - 2.4	12.5	4000	1
83260228	FLEXIMARK® O.shr 2.4/1.2-16.6 YE		1.2 - 2.4	16.6	3000	1
83260100	FLEXIMARK® O.shr 2.4/1.2-25 YE		1.2 - 2.4	25.0	2000	1
83260090	FLEXIMARK® O.shr 2.4/1.2-38 YE		1.2 - 2.4	38.0	1000	1
83260080	FLEXIMARK® O.shr 2.4/1.2-50 YE		1.2 - 2.4	50.0	1000	1
83260226	FLEXIMARK® O.shr 3.2/1.6-12.5 YE		1.6 - 3.2	12.5	4000	1
83260229	FLEXIMARK® O.shr 3.2/1.6-16.6 YE		1.6 - 3.2	16.6	3000	1
83260101	FLEXIMARK® O.shr 3.2/1.6-25 YE		1.6 - 3.2	25.0	2000	1
83260091	FLEXIMARK® O.shr 3.2/1.6-38 YE		1.6 - 3.2	38.0	1000	1
83260081	FLEXIMARK® O.shr 3.2/1.6-50 YE		1.6 - 3.2	50.0	1000	1
83260227	FLEXIMARK® O.shr 4.8/2.4-12.5 YE		2.4 - 4.8	12.5	4000	1
83260230	FLEXIMARK® O.shr 4.8/2.4-16.6 YE		2.4 - 4.8	16.6	3000	1
83260102	FLEXIMARK® O.shr 4.8/2.4-25 YE		2.4 - 4.8	25.0	2000	1
83260092	FLEXIMARK® O.shr 4.8/2.4-38 YE		2.4 - 4.8	38.0	1000	1
83260082	FLEXIMARK® O.shr 4.8/2.4-50 YE		2.4 - 4.8	50.0	1000	1
83260103	FLEXIMARK® O.shr 6.4/3.2-25 YE		3.2 - 6.4	25.0	2000	1
83260093	FLEXIMARK® O.shr 6.4/3.2-38 YE		3.2 - 6.4	38.0	1000	1
83260083	FLEXIMARK® O.shr 6.4/3.2-50 YE		3.2 - 6.4	50.0	1000	1
83260104	FLEXIMARK® O.shr 9.5/4.8-25 YE		4.8 - 9.5	25.0	1000	1
83260094	FLEXIMARK® O.shr 9.5/4.8-38 YE		4.8 - 9.5	38.0	500	1

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03\_16



FLEXIMARK®

			(mm)	(mm)	PU	PU
83260084	FLEXIMARK® O.shr 9.5/4.8-50 YE		4.8 - 9.5	50.0	500	1
83260105	FLEXIMARK® O.shr 12.7/6.4-25 YE		6.4 - 12.7	25.0	1000	1
83260095	FLEXIMARK® O.shr 12.7/6.4-38 YE		6.4 - 12.7	38.0	500	1
83260085	FLEXIMARK® O.shr 12.7/6.4-50 YE		6.4 - 12.7	50.0	500	1
83260106	FLEXIMARK® O.shr 19.1/9.5-25 YE		9.5 - 19.1	25.0	1000	1
83260096	FLEXIMARK® O.shr 19.1/9.5-38 YE		9.5 - 19.1	38.0	500	1
83260086	FLEXIMARK® O.shr 19.1/9.5-50 YE		9.5 - 19.1	50.0	500	1
83260107	FLEXIMARK® O.shr 25.4/12.7-25 YE		12.7 - 25.4	25.0	600	1
83260097	FLEXIMARK® O.shr 25.4/12.7-38 YE		12.7 - 25.4	38.0	300	1
83260087	FLEXIMARK® O.shr 25.4/12.7-50 YE		12.7 - 25.4	50.0	300	1
83260098	FLEXIMARK® O.shr 38.1/19.1-38 YE		19.1 - 38.1	38.0	100	1
83260088	FLEXIMARK® O.shr 38.1/19.1-50 YE		19.1 - 38.1	50.0	100	1
83260099	FLEXIMARK® O.shr 50.8/25.4-38 YE		25.4 - 50.8	38.0	100	1
83260089	FLEXIMARK® O.shr 50.8/25.4-50 YE		25.4 - 50.8	50.0	100	1
83260044	FLEXIMARK® Org.shr. 2.4/0.8-25(2) YE		0.8 - 2.4	25.0	2000	1
83260035	FLEXIMARK® Org.shr. 2.4/0.8-38(1) YE		0.8 - 2.4	38.0	1000	1
83260026	FLEXIMARK® Org.shr. 2.4/0.8-50(1) YE		0.8 - 2.4	50.0	1000	1
83260045	FLEXIMARK® Org.shr. 3.2/1.0-25(2) YE		1.0 - 3.2	25.0	2000	1
83260036	FLEXIMARK® Org.shr. 3.2/1.0-38(1) YE		1.0 - 3.2	38.0	1000	1
83260027	FLEXIMARK® Org.shr. 3.2/1.0-50(1) YE		1.0 - 3.2	50.0	1000	1

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16



FLEXIMARK®

			(mm)	(mm)	PU	PU
83260046	FLEXIMARK® Org.shr. 4.8/1.6-25(2) YE		1.6 - 4.8	25.0	2000	1
83260037	FLEXIMARK® Org.shr. 4.8/1.6-38(1) YE		1.6 - 4.8	38.0	1000	1
83260028	FLEXIMARK® Org.shr. 4.8/1.6-50(1) YE		1.6 - 4.8	50.0	1000	1
83260047	FLEXIMARK® Org.shr. 6.4/2.0-25(2) YE		2.0 - 6.4	25.0	2000	1
83260038	FLEXIMARK® Org.shr. 6.4/2.0-38(1) YE		2.0 - 6.4	38.0	1000	1
83260029	FLEXIMARK® Org.shr. 6.4/2.0-50(1) YE		2.0 - 6.4	50.0	1000	1
83260048	FLEXIMARK® Org.shr. 9.5/3.0-25(2) YE		3.0 - 9.5	25.0	1000	1
83260039	FLEXIMARK® Org.shr. 9.5/3.0-38(1) YE		3.0 - 9.5	38.0	500	1
83260030	FLEXIMARK® Org.shr. 9.5/3.0-50(1) YE		3.0 - 9.5	50.0	500	1
83260049	FLEXIMARK® Org.shr. 12.7/4.0-25(2)YE		4.0 - 12.7	25.0	1000	1
83260040	FLEXIMARK® Org.shr.12.7/4.0-38(1)Y E		4.0 - 12.7	38.0	500	1
83260031	FLEXIMARK® Org.shr.12.7/4.0-50(1)Y E		4.0 - 12.7	50.0	500	1
83260041	FLEXIMARK® Org.shr. 19.0/6.0-38(1)YE		6.0 - 19.0	38.0	500	1
83260032	FLEXIMARK® Org.shr.19.0/6.0-50(1)Y E		6.0 - 19.0	50.0	500	1
83260051	FLEXIMARK® Org.shr. 5.4/8.0-25(2)YE		8.0 - 25.4	25.0	600	1
83260042	FLEXIMARK® Org.shr.25.4/8.0-38(1)Y E		8.0 - 25.4	38.0	300	1
83260033	FLEXIMARK® Org.shr. 25.4/8.0-50(1)YE		8.0 - 25.4	50.0	300	1
83260043	FLEXIMARK® Org.shr. 38.1/12.7-38(1)YE		12.7 - 38.1	38.0	100	1
83260034	FLEXIMARK® Org.shr. 38.1/12.7-75(1)YE		12.7 - 38.1	75.0	100	1

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16



FLEXIMARK®

			(mm)	(mm)	PU	PU
83260050	FLEXIMARK® Org. shr.19.0/6.0-25(2)YE		6.0 - 19.0	25.0	1000	1

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16