

FLEXIMARK® TA

FLEXIMARK®
)



UV-

Easy to print via FLEXIMARK®
software Flexisoft and FLEXIMARK®

thermal transfer printer SQUIX, EOS5 or EOS2
Recommended ribbon: FTI-Y 60-360 BK (article no. 83260201)

(24.04.2024)



FLEXIMARK® TA

ETIM 5:

ETIM 5.0 Class-ID: EC001288

ETIM 5.0 class :

:

:

:

:

-40 °C +90 °C

가	VAT	가	가) LCK 32	640	640	1	PU
FLEXIMARK®								

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



FLEXIMARK® TA

		(mm)	m / PU	PU
83255355	FLEXIMARK® TA foam 13-20m SR	13	20	1
83255356	FLEXIMARK® TA foam 15-20m SR	15	20	1
83255357	FLEXIMARK® TA foam 18-20m SR	18	20	1
83255358	FLEXIMARK® TA foam 25-20m SR	25	20	1
83255359	FLEXIMARK® TA foam 30-20m SR	30	20	1
83255360	FLEXIMARK® TA foam 35-20m SR	35	20	1
83255361	FLEXIMARK® TA foam 50-20m SR	50	20	1
83255362	FLEXIMARK® TA foam 80-20m SR	80	20	1
83255363	FLEXIMARK® TA foam 100-20m SR	100	20	1

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16