

FLEXIMARK® TA

TA

가

가



가

가

Easy to print via FLEXIMARK®
software Flexisoft and FLEXIMARK®

thermal transfer printer SQUIX, EOS5 or EOS2
: R71 110-360 BK (83259609)
More sizes and colours available on request

(24.04.2024)



FLEXIMARK® TA

ETIM 5:

ETIM 5.0 Class-ID: EC001288

ETIM 5.0 class :

: 15 N/mm

:

:

,

:

(0.1 mm)

:

-40°C ~ +150°C 가 : +10°C

가 VAT
FLEXIMARK®

가 가 .

.) LCK 32

640

640

1

PU

(24.04.2024)



FLEXIMARK® TA

			x (mm)	PU	PU
83259611	FLEXIMARK® YE	TA 15-6	15.6 x 6.0	10000	1
83259628	FLEXIMARK® YE	TA 18-9	18.0 x 9.0	10000	1
83259634	FLEXIMARK® YE	TA 20-8	20.0 x 8.0	10000	1
83259641	FLEXIMARK® 25.4-12.7 YE	TA	25.4 x 12.7	10000	1
83259653	FLEXIMARK® YE	TA 26-10	26.0 x 10.0	10000	1
83259664	FLEXIMARK® 26.5-17.5 YE	TA	26.5 x 17.5	5000	1
83259683	FLEXIMARK® 32-9.5 YE	TA	32.0 x 9.5	10000	1
83259594	FLEXIMARK® YE	TA 37-9	37.0 x 9.0	2000	1
83259574	FLEXIMARK® YE	TA 38-13	38.0 x 13.0	5000	1
83259694	FLEXIMARK® YE	TA 38-19	38.0 x 19.0	2000	1
83259700	FLEXIMARK® YE	TA 45-23	45.0 x 23.0	2000	1
83259706	FLEXIMARK® YE	TA 47-28	47.0 x 28.0	1500	1
83259712	FLEXIMARK® YE	TA 50-23	50.0 x 23.0	2000	1
83259718	FLEXIMARK® YE	TA 60-36	60.0 x 36.0	1000	1
83259724	FLEXIMARK® YE	TA 65-35	65.0 x 35.0	1000	1
83259736	FLEXIMARK® YE	TA 70-48	70.0 x 48.0	1000	1
83259783	FLEXIMARK® YE	TA 75-28	75.0 x 28.0	2000	1
83259755	FLEXIMARK® 101.6-23 YE	TA	101.6 x 23.0	2000	1
83259763	FLEXIMARK® 101.6-36 YE	TA	101.6 x 36.0	1000	1
83259610	FLEXIMARK® WH	TA 15-6	15.0 x 6.0	10000	1
83259629	FLEXIMARK®	TA 18-9	18.0 x 9.0	10000	1

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03_16



FLEXIMARK® TA

			x (mm)	PU	PU
	WH				
83259635	FLEXIMARK® WH	TA 20-8	20.0 x 8.0	10000	1
83259643	FLEXIMARK® 25.4-12.7 WH	TA	25.4 x 12.7	10000	1
83259655	FLEXIMARK® WH	TA 26-10	26.0 x 10.0	10000	1
83259665	FLEXIMARK® 26.5-17.5 WH	TA	26.5 x 17.5	5000	1
83259685	FLEXIMARK® 32-9.5 WH	TA	32.0 x 9.5	10000	1
83259593	FLEXIMARK® WH	TA 37-9	37.0 x 9.0	2000	1
83259573	FLEXIMARK® WH	TA 38-13	38.0 x 13.0	5000	1
83259695	FLEXIMARK® WH	TA 38-19	38.0 x 19.0	2000	1
83259701	FLEXIMARK® WH	TA 45-23	45.0 x 23.0	2000	1
83259707	FLEXIMARK® WH	TA 47-28	47.0 x 28.0	1500	1
83259713	FLEXIMARK® WH	TA 50-23	50.0 x 23.0	2000	1
83259719	FLEXIMARK® WH	TA 60-36	60.0 x 36.0	1000	1
83259725	FLEXIMARK® WH	TA 65-35	65.0 x 35.0	1000	1
83259737	FLEXIMARK® WH	TA 70-48	70.0 x 48.0	1000	1
83259782	FLEXIMARK® WH	TA 75-28	75.0 x 28.0	2000	1
83259756	FLEXIMARK® 101.6-23 WH	TA	101.6 x 23.0	2000	1
83259764	FLEXIMARK® 101.6-36 WH	TA	101.6 x 36.0	1000	1
83259673	FLEXIMARK® WH	TA 30-20	30.0 x 20.0	6000	1

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16