

FLEXIMARK® NM Stainless steel - character holders

FLEXIMARK®

NM

FLEXIMARK® PR 1 NM 7(: M3251010)



MR

(: 가 ,)

가

JQS

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

FLEXIMARK® NM Stainless steel - character holders

(7.9 mm) (3 mm Ø)

ETIM 5: ETIM 5.0 Class-ID: EC001288
ETIM 5.0 class :

ETIM 6: ETIM 6.0 Class-ID: EC001288
ETIM 6.0 Class :

Dimensions: +/- 1,5mm
: : 11 mm
Ø: 3 mm

: Acid resistant stainless steel
EN 1.4404 (SS2348, AISI 316L)
:-80°C~+500°C

가 VAT 가 가 .) LCK 32 640 640 1 PU
FLEXIMARK®



FLEXIMARK® NM Stainless steel - character holders

		(mm)		PU	PU
83254214	FLEXIMARK® PR10 NM4	48.0	6	50	1
83254213	FLEXIMARK® PR10 NM5	60.0	8	50	1
83254212	FLEXIMARK® PR10 NM7	84.0	12	50	1
83254211	FLEXIMARK® PR10 NM9	108.0	16	50	1
83254215	FLEXIMARK® PR10 NM11	176.0	26	50	1
83254210	FLEXIMARK® PR10 NM24	288.0	46	50	1

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16