

PROFINET

HITRONIC® PCF

PVC PUR , PROFINET B C

PROFINET 2K 200/230 PCF B C,
 J-VY (ZN) Y, AT-V (ZN) Y (ZN) 11Y

PROFINET
 - B C



Lapp



500m

(24.04.2024)



PROFINET

HITRONIC® PCF

PCF DUPLEX
PROFINET / Industrial Ethernet
100 Mbit/s: 100 m
PROFINET B :
PROFINET C : ()

PVC 가 :

PUR 가 :

PNB - PROFINET-Type B
PNC - PROFINET-Type C
FD - Highly flexible ()

28055702 : C (UL)
(OFNG 75 ° C)
PUR compound: oil resistant acc. to IEC 60811-2-1 und DIN EN 50363-10-2

PVC , PCF
: 2.2mm
(Aramid Yarns)
PUR PVC ()
: (RAL 6018)

ETIM 5: ETIM 5.0 Class-ID: EC000034
ETIM 5.0 Class-Description:

ETIM 6: ETIM 6.0 Class-ID: EC000034
ETIM 6.0 Class : LWL

: Buffered fibre: 0.5mm
Single cable: 2.2 mm

: , ()

Fibre type: PCF - K200/230
PCF - Polymer Cladded Fibre

:: J-V(ZN)YY 2K200/230
J-V(ZN)Y(ZN)11Y 2K200/230 flex
J-V(ZN)Y(ZN)Y 2K200/230 flex

: :

가 :

(24.04.2024)



PROFINET

HITRONIC® PCF

:

Lapp Kabel PROFIBUS user organisation (PNO) 가 가 . (.) 가 .

가 VAT 가 가 .

(24.04.2024)



PROFINET

HITRONIC® PCF

		Fibre type	Number of fibres	(mm)	(kg/km)
28052702	HITRONIC® PCF DUPLEX PNB PVC-PVC	200/230 PCF	2	7.2	55
PCF DUPLEX - PROFINET TYPE C					
28351702	HITRONIC® PCF DUPLEX FD PNC PVC-PUR	200/230 PCF	2	8.8	71
28352702	HITRONIC® PCF DUPLEX FD PNC PVC-PVC	200/230 PCF	2	8.8	76

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16