

# HITRONIC® BUS PCF DUPLEX indoor + outdoor

HITRONIC® PCF DUPLEX , , 2.9 mm, A-VQ (ZN) HB2Y 2K200/230  
J-V (ZN) H11Y



500m

EMC

PROFIBUS, INTERBUS

가 : 650nm, 850nm  
BUS

FRNC 가 PCF (2.9mm)  
(Aramid Yarns)  
: PUR; PE  
: ( ), ( )

ETIM 5:

ETIM 5.0 Class-ID: EC000034  
ETIM 5.0 Class-Description:

(24.04.2024)

# HITRONIC® BUS PCF DUPLEX indoor + outdoor

ETIM 6:	ETIM 6.0 Class-ID: EC000034
:	ETIM 6.0 Class : LWL
:	Buffered fibre: 0.5mm
:	Single cable: 2.9 mm
:	:
:	,
Fibre type:	PCF - K200/230
:	PCF - Polymer Cladded Fibre
:	: 15 x
:	: 20 x
::	PCF DUPLEX Indoor: J-V(ZN)H11Y 2K200/230
:	PCF DUPLEX Outdoor: A-VQ(ZN)HB2Y 2K200/230
:	:
:	:
가 :	: 400N( ), 500N( )
:	: 1,200N( ), 1,500N( )
:	: -20 ~ +70 °C
:	: -10°C +50°C

가 VAT 가 가 . ( . ) 가 .



HITRONIC® BUS PCF DUPLEX indoor + outdoor

		Fibre type	Number of fibres	(mm)	(kg/km)
Indoor					
28020702	HITRONIC® PCF DUPLEX FRNC-PUR Indoor	200/230 PCF	2	8	53
Outdoor					
28620702	HITRONIC® PCF DUPLEX FRNC-PE Outdoor	200/230 PCF	2	10.5	89

(24.04.2024)

©2024 Lapp Group - all rights reserved.  
<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16