

# HITRONIC® POF DUPLEX CABLE

PUR ,

HITRONIC® POF DUPLEX PE PE , PUR ,

J-V2Y (ZN) 11Y 2P980/1000



Ethernet



70m

FD : ( )

(24.04.2024)

# HITRONIC® POF DUPLEX CABLE

가  
 , ,  
 FD :  
 5.000.000

(POF)  
 PE  
 Fibre : ,  
 (Aramid Yarns)  
 PUR , (RAL 2003)

ETIM 5:	ETIM 5.0 Class-ID: EC000034
	ETIM 5.0 Class-Description:
ETIM 6:	ETIM 6.0 Class-ID: EC000034
	ETIM 6.0 Class : LWL
:	: 2.2mm
:	:
Fibre type:	2x
	POF - P980/1000
::	J-V2Y(ZN)11Y
:	: PMMA
:	:
가 :	10 x
가 :	: 100 N (PE-PUR),
	130 N (Heavy PE-PUR)
	- : 400 N
:	: -40°C ~+7°C
	(FD: -20°C ~+70°C)
	: -10°C +50°C

가 가 ( . ) 가  
[www.lappkabel.de/en/cable-standradlengths](http://www.lappkabel.de/en/cable-standradlengths)

가 VAT 가 가 .



# HITRONIC® POF DUPLEX CABLE

		Fibre type	Number of fibres	(mm)	(kg/km)
HITRONIC® POF DUPLEX PE-PUR					
28020002	HITRONIC® POF DUPLEX PE-PUR	980/1000 POF	2	5.5	27
HITRONIC® POF DUPLEX HEAVY PE-PUR					
28030002	HITRONIC® POF DUPLEX HEAVY PE-PUR	980/1000 POF	2	8	57
HITRONIC® POF DUPLEX FD PE-PUR					
28320002	HITRONIC® POF DUPLEX FD PE-PUR	980/1000 POF	2	6	30

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16

# HITRONIC® POF DUPLEX CABLE



(24.04.2024)