

# NHXMH

; 가 ,  
NHXMH, 가 , , +70 °C

CPR: [www.lappkabel.com/cpr](http://www.lappkabel.com/cpr)  
, PVC NYM



, 가  
가

: IEC 60332-1-2  
IEC 60332-3-24 , 가

VDE 0250 214

: PE

(24.04.2024)

# NHXMH

:

ETIM 5:

ETIM 5.0 Class-ID: EC000043  
ETIM 5.0

ETIM 6:

ETIM 6.0 Class-ID: EC000043  
ETIM 6.0 Class :

:

5 : VDE 0293-308  
6 :

T9

:

-

:

: 4 x

:

U0/U: 300/500 V

:

2000 V

:

G = GN/YE

X = GN/YE

:

: +70°C

, 가 가 ( . ) 가 .  
www.lappkabel.de/en/cable-standradlengths  
: 30 kg or 250 m,  
(e.g. 1 x 500 m or 5 x 100 m ).

가 VAT 가 가 .

(24.04.2024)



NHXMH

Article number	(CORE) / (mm <sup>2</sup> )	(mm)	(kg/km)	(kg/km)
16020003	3 G 1,5	8.5	43	120
16020013	4 G 1,5	9.3	58	145
16020023	5 G 1,5	10	72	170
1602003	7 G 1,5	10.8	101	210
16020103	3 G 2,5	9.4	72	160
16020123	5 G 2,5	11	120	230

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16