

H07Z1-K Type 2

Harmonised,

H07Z1-K Type 2, <HAR>, halogen-free single core, +70°C, harmonised, for wiring in control cabinets, nominal voltage 450/750V

CPR: www.lappkabel.com/cpr
(HAR), +70°C

H07Z-K 90°C



가 가 가

H07Z-K 90°C

가

가
IEC 61034 , /
IEC 60332-1-2 IEC 60332-3-24

EN 50525-3-31/VDE 0285-525-3-31 <HAR>

(24.04.2024)

©2024 Lapp Group - all rights reserved.
<http://lappkorea.lappgroup.com>
data sheet

PN 0456 / 02_03.16

H07Z1-K Type 2

가

ETIM 5:

ETIM 5.0 Class-ID: EC000993

ETIM 5.0 Class :

VDE 0295 5/ IEC 60228 5

가 가

EN 50565-1

OD 8 mm: 4 x OD*/2 x OD**;

8 < OD 12 mm: 5 x OD*/3 x OD**;

OD > 12 mm: 6 x OD*/4 x OD**

U0/U: 450/ 750 V

2500 V

VDE 0298-4

EN 50565-1/ VDE 0298-565-1

: +5°C ~ +70°C

: -40°C ~ +70°C

30 kg,

가

가

(.)

가

가

VAT

가

가

; "OD" =

H07Z1-K Type 2

	(mm ²)	(mm)		m/	(kg/km)	(kg/km)
4724060	1.5	2.8 - 3.4		100	14.4	20
4724061	1.5	2.8 - 3.4		100	14.4	20
4724062	1.5	2.8 - 3.4		100	14.4	20
4724063	1.5	2.8 - 3.4		100	14.4	20
4724064	1.5	2.8 - 3.4	/	100	14.4	20
4724065	2.5	3.4 - 4.1		100	24	32
4724066	2.5	3.4 - 4.1		100	24	32
4724067	2.5	3.4 - 4.1		100	24	32
4724068	2.5	3.4 - 4.1		100	24	32
4724069	2.5	3.4 - 4.1	/	100	24	32
4724070	4	3.9 - 4.8		100	38	45
4724071	4	3.9 - 4.8		100	38	45
4724072	4	3.9 - 4.8		100	38	45
4724073	4	3.9 - 4.8		100	38	45
4724074	4	3.9 - 4.8	/	100	38	45
4724075	6	4.4 - 5.3		100	58	65
4724076	6	4.4 - 5.3		100	58	65
4724077	6	4.4 - 5.3		100	58	65
4724078	6	4.4 - 5.3		100	58	65
4724079	6	4.4 - 5.3	/	100	58	65
4724080	10	5.7 - 6.8		100	96	110
4724081	10	5.7 - 6.8		100	96	110
4724082	10	5.7 - 6.8		100	96	110
4724083	10	5.7 - 6.8		100	96	110
4724084	10	5.7 - 6.8	/	100	96	110
4724085	16	6.7 - 8.1		100	154	170
4724086	16	6.7 - 8.1		100	154	170
4724087	16	6.7 - 8.1		100	154	170
4724088	16	6.7 - 8.1		100	154	170
4724089	16	6.7 - 8.1	/	100	154	170

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03_16