

H05V-K in big one-way cardboard box

H05V-K, HAR, , PVC, 300 / 500V, , class 5/

CPR: www.lappkabel.com/cpr

<HAR>



가

가 가 가

: IEC 60332-1-2

EN 50525-2-31 <HAR>

5(IEC 60228)
: PVC

가 가

ETIM 5:

ETIM 5.0 Class-ID: EC000993

(24.04.2024)

H05V-K in big one-way cardboard box

ETIM 6:	ETIM 5.0 Class :
:	ETIM 6.0 Class-ID: EC000993
:	ETIM 6.0 Class :
:	VDE 0295 5/ IEC 60228 5
:	가 가
:	EN 50565-1
:	4 x (OD), 2 x OD
:	U0/U: 300/500 V
:	2000 V
:	VDE 0298 4
:	EN 50565-1/ VDE 0298-565-1
:	: -40°C +70°C

가 VAT 가 가 . 가 가 . (.) 가 .

H05V-K in big one-way cardboard box

		(mm ²)	(mm)	m/box	(kg/km)	(kg/km)
4510001K	/	0.5	2.1 - 2.5	3000	4.8	9
4511065K		0.5	2.1 - 2.5	3000	4.8	9
4510011K		0.5	2.1 - 2.5	3000	4.8	9
4511073K		0.5	2.1 - 2.5	3000	4.8	9
4510021K		0.5	2.1 - 2.5	3000	4.8	9
4510021E		0.5	2.1 - 2.5	9000	4.8	9
4511064K		0.5	2.1 - 2.5	3000	4.8	9
4511060E		0.5	2.1 - 2.5	9000	4.8	9
4510161K		0.5	2.1 - 2.5	3000	4.8	9
4511070K		0.5	2.1 - 2.5	3000	4.8	9
4511068K		0.5	2.1 - 2.5	3000	4.8	9
4511072K		0.5	2.1 - 2.5	3000	4.8	9
4511071K		0.5	2.1 - 2.5	3000	4.8	9
4510921K	/	0.5	2.1 - 2.5	3000	4.8	9
4510002K	/	0.75	2.2 - 2.7	2500	7.2	12
4510122K		0.75	2.2 - 2.7	2500	7.2	12
4510032K		0.75	2.2 - 2.7	2500	7.2	12
4510012K		0.75	2.2 - 2.7	2500	7.2	12
4510062K		0.75	2.2 - 2.7	2500	7.2	12
4510022K		0.75	2.2 - 2.7	2500	7.2	12
4510022E		0.75	2.2 - 2.7	7500	7.2	12
4510142K		0.75	2.2 - 2.7	2500	7.2	12
4511061E		0.75	2.2 - 2.7	7500	7.2	12
4510162K		0.75	2.2 - 2.7	2500	7.2	12
4510092K		0.75	2.2 - 2.7	2500	7.2	12
4510072K		0.75	2.2 - 2.7	2500	7.2	12
4510112K		0.75	2.2 - 2.7	2500	7.2	12
4510052K		0.75	2.2 - 2.7	2500	7.2	12
4510042K		0.75	2.2 - 2.7	2500	7.2	12
4510042E		0.75	2.2 - 2.7	7500	7.2	12
4510082K		0.75	2.2 - 2.7	2500	7.2	12
4510262K	/	0.75	2.2 - 2.7	2500	7.2	12
4510922K	/	0.75	2.2 - 2.7	2500	7.2	12
4510003K	/	1	2.4 - 2.8	2000	9.6	15

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

H05V-K in big one-way cardboard box

		(mm ²)	(mm)	m/box	(kg/km)	(kg/km)
4510033K		1	2.4 - 2.8	2000	9.6	15
4510013K		1	2.4 - 2.8	2000	9.6	15
4510013E		1	2.4 - 2.8	6000	9.6	15
4510063K		1	2.4 - 2.8	2000	9.6	15
4510023K		1	2.4 - 2.8	2000	9.6	15
4510023E		1	2.4 - 2.8	6000	9.6	15
4510143K		1	2.4 - 2.8	2000	9.6	15
4511062E		1	2.4 - 2.8	6000	9.6	15
4510163K		1	2.4 - 2.8	2000	9.6	15
4510093K		1	2.4 - 2.8	2000	9.6	15
4510073K		1	2.4 - 2.8	2000	9.6	15
4510113K		1	2.4 - 2.8	2000	9.6	15
4510053K		1	2.4 - 2.8	2000	9.6	15
4510043K		1	2.4 - 2.8	2000	9.6	15
4510043E		1	2.4 - 2.8	6000	9.6	15
4510083K		1	2.4 - 2.8	2000	9.6	15
4510263K	/	1	2.4 - 2.8	2000	9.6	15
4510923K	/	1	2.4 - 2.8	2000	9.6	15

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

H05V-K in big one-way cardboard box



(24.04.2024)

©2024 Lapp Group - all rights reserved.
<http://lappkorea.lappgroup.com>
data sheet

PN 0456 / 02_03.16