


H05BQ-F / H07BQ-F

PUR (HAR)가

PUR power cable, harmonized according H05BQ-F / H07BQ-F type for oil and abrasion resistant use with handheld equipment or building machines

H05BQ-F/H07BQ-F



PUR

가

가

(24.04.2024)

H05BQ-F / H07BQ-F

가 , -40°C

EN 50525-2-21
H05BQ-F/H07BQ-F

:

PUR

:

ETIM 5:

ETIM 5.0 Class-ID: EC001578
ETIM 5.0 Class 가

ETIM 6:

ETIM 6.0 Class-ID: EC001578
ETIM 6.0 Class :

:

VDE 0293-308 , T9

:

IEC 60228/VDE 0295 class 5

:

:
12.5 x
: 4 x

:

1.0 mm²: U0/U: 300/500 V

:

3000 V

:

G = GN/YE

X = GN/YE

:

: -40°C ~ +90°C
: -50°C +90°C

가 가 (.) 가 .
www.lappkabel.de/en/cable-standradlengths
: 30 kg or 250 m,
(e.g. 1 x 500 m or 5 x 100 m).

가 VAT 가 가 .

(24.04.2024)



H05BQ-F / H07BQ-F

Article number	(CORE) / (mm ²)	(mm)	(kg/km)	(kg/km)
H05BQ-F U0/U: 300/500 V				
0013600	2 X 0.75	5.7 - 7.4	14.4	50
0013601	3 G 0.75	6.2 - 8.1	21.6	64
00136023	4 G 0.75	6.8 - 8.8	28.8	78
00136033	5 G 0.75	7.6 - 9.9	36	98
0013610	2 X 1.0	6.1 - 8	19.2	60
0013611	3 G 1.0	6.5 - 8.5	29	74
00136123	4 G 1.0	7.1 - 9.3	38.4	92
00136133	5 G 1.0	8 - 10.3	48	114
H07BQ-F U0/U: 450/750 V				
0013620	2 X 1.5	7.6 - 9.8	29	87
0013621	3 G 1.5	8 - 10.4	43	108
00136223	4 G 1.5	9 - 11.6	58	137
00136233	5 G 1.5	9.8 - 12.7	72	165
0013630	2 X 2.5	9 - 11.6	48	90
0013631	3 G 2.5	9.6 - 12.4	72	161
00136323	4 G 2.5	10.7 - 13.8	96	206
00136333	5 G 2.5	11.9 - 16.3	120	254

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16