

H01N2-D

H01N2-D, HAR- , , NSLFFÖU , 100VAC, 150VDC, HD 22.6, EN 50525-2-81, IEC 60245

EN 50525-2-81
VDE NSLFFÖU



가 <HAR> - CENELEC 가 "<HAR>"

EN 50565-2
100V 가

: IEC 60332-1-2

H01N2-D

EN 50525-2-81 <HAR> H01N2-D

HAR
VDE 0295 , 95 mm² class 6 , 120 mm² class 5

: , type EM5

ETIM 5:	ETIM 5.0 Class-ID: EC000824
	ETIM 5.0 class :
ETIM 6:	ETIM 6.0 Class-ID: EC000824
	ETIM 6.0 Class :
:	EN 50525-2-81 H01N2-D
:	: 12 x
:	U0/U: 100/100 V
:	1000V
:	VDE 0298 Part 4, 16
:	EN 50565-1/ VDE 0298-565-1
:	Flexible use: -20°C to +85°C

가 가 . (.) 가 .
www.lappkabel.de/en/cable-standradlengths
: 30 kg or 250 m,
(e.g. 1 x 500 m or 5 x 100 m).
가 VAT 가 가 .

(24.04.2024)



H01N2-D

Article number	(mm ²)	(mm)	(kg/km)	(kg/km)
2310026	10	7.7 - 8.7	96	171
2210700	16	8.8 - 9.8	153.6	198
2210701	25	10.1 - 11.3	240	305
2210702	35	11.4 - 12.6	336	415
2210703	50	13.2 - 14.6	480	555
2210704	70	15.3 - 16.9	672	765
2210705	95	17.1 - 18.8	912	1010
2210706	120	19.2 - 21.1	1152	1262
2210707	150	21.1 - 23.2	1440	1610
2210708	240	25.8 - 27.7	2304	2520

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16