

H05RN-F

H05RN-F, HAR, , , 300/500V, class 5/ -25°C ~ +60°C, 가 , ,



가 <HAR> - CENELEC 가 "<HAR>"

EN 50565-2 : 가 +60°C, 가 , +50°C ;

: IEC 60332-1-2
EN 60811-404

EN 50525-2-21 <HAR>

H05RN-F

HAR

: EI 4
: , type EM2

ETIM 5:

ETIM 5.0 Class-ID: EC001578
ETIM 5.0 Class 가

ETIM 6:

ETIM 6.0 Class-ID: EC001578
ETIM 6.0 Class :

:

HD 308

:

VDE 0295 5/ IEC 60228 5
가 가

:

4 ~ 8 x (EN 50565-1)

:

U0/U: 300/500 V

:

2000 V

:

G = GN/YE

X = GN/YE

:

IEC 60364-5-52/ VDE 0298-4
EN 50565-1/ VDE 0298-565-1

:

Fixed installation: -25°C up to +60°C
Occasionally moved: -25°C bis +60°C

가 가 (.) 가 .
www.lappkabel.de/en/cable-standradlengths
: 30 kg or 250 m,
(e.g. 1 x 500 m or 5 x 100 m).

가 VAT 가 가 .



H05RN-F

Article number	(CORE) / (mm ²)	(mm)	(kg/km)	(kg/km)
1600250	2 X 0.75	5.7 - 6.7	14.4	55
1600252	3 G 0.75	6.2 - 7.4	21.6	68
16002583	4 G 0.75	6.8 - 7.9	28.8	81
1600251	2 X 1.0	6.1 - 7.3	19.2	63
1600253	3 G 1.0	6.5 - 7.7	28.8	78

(01.05.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16