

NSGAFÖU 1,8/3 kV

1.8/3 kV 가

NSGAFÖU 1,8/3 kV AC, VDE- , 가 , Class 5,



VDE 0250 Part 602 , U0/U: 1.8/3 kV
VDE 0298 Part 3 , 1000V

NSGAFÖU

VDE 0100 Part 520

1000V
가

: IEC 60332-1-2
EN 60811-404

U0/U 0.6/1 kVac 3.6/6 kVac 가

<VDE> NSGAFÖU VDE 0250-602 1,8/3 kV

NSGAFÖU 1,8/3 kV

: 3GI3
: , 5GM3

ETIM 5: ETIM 5.0 Class-ID: EC000993
ETIM 5.0 Class :

ETIM 6: ETIM 6.0 Class-ID: EC000993
ETIM 6.0 Class :

: VDE 0295 5/ IEC 60228 5
가 가
: : 10 x
: 6 x

: U0/U: 1.8/3 kV

: 6000 V

: VDE 0298 Part 4, 15

: During laying: -25 up to +80°C
: -40°C ~ +90°C

, 가 가 . (.) 가 .
www.lappkabel.de/en/cable-standradlengths
: ≤ 30 kg or ≤ 250 m,
(e.g. 1 x 500 m or 5 x 100 m).

가 VAT 가 가 .

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



NSGAFÖU 1,8/3 kV

Article number	(mm ²)	(mm)	(kg/km)	(kg/km)
1600300	1.5	7	14.4	60
1600301	2.5	7.5	24	70
1600302	4	9	38.4	90
1600303	6	9.5	57.6	120
1600304	10	11	96	180
1600305	16	13	153.6	250
1600306	25	15	240	390
1600307	35	16.5	336	470
1600308	50	18	480	625
1600309	70	20.5	672	880
1600310	95	24	912	1190
1600311	120	26	1152	1430
1600312	150	28	1440	1750
1600313	185	31	1776	2160
1600314	240	34.5	2304	2640
3026826	300	38	2880	3545