

ÖLFLEX® PLUG H05VV-F

PVC

ÖLFLEX® PLUG H05VV-F Net connecting cable, PVC, 1-2,5mm², 1.end angled earthing-type plug with double earthed contact/2.end IEC coupling or dismantled

가



PVC H05VV-F 가 , EN 50565-2 UV , www.lappkabel.de

1st end: Gated, right-angled earthing-type plug with double earthing contact
: , 3 IEC

ETIM 5:	ETIM 5.0 Class-ID: EC001576
	ETIM 5.0 Class :
ETIM 6:	ETIM 6.0 Class-ID: EC001576
	ETIM 6.0 Class-Description: Power cord
:	VDE 0293-308 (T9)
:	VDE 0295 5/ IEC 60228 5
:	가 가
:	U0: 250 V AC

(24.04.2024)



ÖLFLEX® PLUG H05VV-F

: 2000 V
 : G = GN/YE
 : 5°C ~ 60°C

* , 가 가 . (.) 가 .
 ,
 가 VAT 가 가 .
 DIN VDE 0620-1 .가 " - 1: ,
 E: "

(24.04.2024)

	(CORE) / (mm ²)	(mm)	(m)	kg/1.000 pieces
1st end: moulded right-angled earthing-type plug with double earthed contact 2nd end: straight, 3-pin C13 IEC coupling, moulded				
73222334	3 G 1.0	6.3 - 8	2.5	72
73222336	3 G 1.0	6.3 - 8	2.5	72
73222381	3 G 1.5	7.4 - 9.4	5	216
73222335	3 G 1.0	6.3 - 8	2.5	72
2nd end: right-angled, 3-pin C13 IEC coupling, moulded				
74320106	3 G 1.5	7.4 - 9.4	3.5	151.2
74320092	3 G 1.5	7.4 - 9.4	7.5	324
1st end: moulded right-angled earthing-type plug with double earthed contact 2nd end: 30 mm stripped, with conductor end sleeves				
70261139	3 G 1.0	6.3 - 8	1.5	43.2
70261140	3 G 1.0	6.3 - 8	2	57.6
70261141	3 G 1.0	6.3 - 8	3	86.4
70261166	3 G 1.0	6.3 - 8	5	144
70261145	3 G 1.0	6.3 - 8	1.5	43.2
70261146	3 G 1.0	6.3 - 8	2	57.6
70261147	3 G 1.0	6.3 - 8	3	86.4
70261143	3 G 1.0	6.3 - 8	2	57.6
70261144	3 G 1.0	6.3 - 8	3	86.4
70261148	3 G 1.5	7.4 - 9.4	1.5	64.5
70261149	3 G 1.5	7.4 - 9.4	2	86
70261150	3 G 1.5	7.4 - 9.4	3	129
70261160	3 G 1.5	7.4 - 9.4	5	215
70261185	3 G 1.5	7.4 - 9.4	1	43.2
70261154	3 G 1.5	7.4 - 9.4	1.5	64.5
70261155	3 G 1.5	7.4 - 9.4	2	86
70261156	3 G 1.5	7.4 - 9.4	3	129
70362272	3 G 1.5	7.4 - 9.4	4	172
70261151	3 G 1.5	7.4 - 9.4	1.5	64.5
70261152	3 G 1.5	7.4 - 9.4	2	86
70261153	3 G 1.5	7.4 - 9.4	3	129
70261163	3 G 2.5	9.2 - 11.4	3	216