

SEW

ÖLFLEX® SERVO Core Line(PUR)

ETIM 5:

ETIM 5.0 Class-ID: EC000104

ETIM 5.0

:

:

: V / L2

:

U/L2/C/L +

: W/L3/D/L-GN/YE

: WS; SW

:

IEC 60228/VDE 0295 class 5

:

Chain application: 7,5 x cable diameter

: 4 x

:

:

U0/U: 600/1000 V

UL & CSA: 1000 V

:

Core/Core: 4 kV

Core/Screen: 4 kV

:

G = GN/YE

:

: -40 ~ 90°C(UL/CSA: 80°C)

: -50 ~ 90°C(UL/CSA: 80°C)

:

5 mio. cycles

SEW® SEW Eurodrive GmbH & Co KG, Ernst-Blickle Str. 42, D-76646 Bruchsal

Lapp

가 VAT 가 가

Further Article and length online <https://servoconfigurator.lappgroup.com/>

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



SEW

ÖLFLEX® SERVO Core Line(PUR)

	(m)	LENZE®	OD in mm	Cable cross section	kg/1.000 pieces
5440000174	10.0	13331221	12.9	4G1,5+(3x1,0)	1,514.1
5440000175	10.0	13332155	14.1	4G2,5+(3x1,0)	1,909.44
5440000176	10.0	13332163	16.3	4G4+(3x1,0)	2,844.45

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16