

# ÖLFLEX® CHAIN 819 P

PVC

-

ÖLFLEX® CHAIN 819 P - PVC

PU-

- 가

UL/cUL



가

, 가 ,

, ,

(24.04.2024)

# ÖLFLEX® CHAIN 819 P

Indoor applications or dry rooms

IEC/EN: 60332-1-2  
UL/CSA: , FT2

: UL AWM Style 21576  
: cUL AWM Style I/II A FT2  
UL File No. E63634  
: 가 T3

: PVC

Lapp-PU-Special Blend ( , RAL 9005)

ETIM 5:

ETIM 5.0 Class-ID: EC000104  
ETIM 5.0

Black with white numbers acc. to VDE 0293-334

VDE 0295 5/ IEC 60228 5  
가 가

Flexing: up from 10 x outer diameter  
: 4 x

IEC U0/U: 300/500 V  
UL: 1,000V

Core/core: 4000 V

G = GN/YE  
X = GN/YE

: -5°C ~ +70°C (UL: +80°C)  
: -40°C ~ +70°C(UL: +80°C)

A2-1

[www.lappkabel.de/en/cable-standradlengths](http://www.lappkabel.de/en/cable-standradlengths)

: 30 kg or 250 m,

(e.g. 1 x 500 m or 5 x 100 m ).

가 VAT 가 가 .

(24.04.2024)



# ÖLFLEX® CHAIN 819 P

Article number	(CORE) / (mm <sup>2</sup> )	(mm)	(kg/km)	(kg/km)
1027800	2 X 0.5	5.2	9.6	30.7
1027801	3 G 0.5	5.5	14.4	39.2
1027802	4 G 0.5	6	19.2	48.5
1027803	5 G 0.5	6.5	24	58
1027804	7 G 0.5	7.7	33.6	79
1027805	12 G 0.5	9.2	57.6	121.1
1027806	18 G 0.5	11	86.4	177.9
1027807	25 G 0.5	13.3	120	250
1027810	2 X 0.75	5.6	14.4	37.9
1027811	3 G 0.75	6	21.6	49.4
1027812	4 G 0.75	6.5	28.8	61.5
1027813	5 G 0.75	7.1	36	74.5
1027814	7 G 0.75	8.5	50.4	105.6
1027815	12 G 0.75	10.3	86.4	163.3
1027816	18 G 0.75	12.2	129.6	239
1027817	25 G 0.75	14.8	180	334.8
1027820	2 X 1.0	5.9	19.2	43.1
1027821	3 G 1.0	6.3	28.8	56.5
1027822	4 G 1.0	6.9	39	71.3
1027823	5 G 1.0	7.5	48	86.2
1027824	7 G 1.0	9	67	122.3
1027825	12 G 1.0	10.9	115.2	190.3
1027826	18 G 1.0	13.2	172.8	285.4
1027827	25 G 1.0	15.7	240	391.2
1027830	2 X 1.5	6.5	28.8	55.6
1027831	3 G 1.5	6.9	43.2	74.5
1027832	4 G 1.5	7.6	58	94.7
1027833	5 G 1.5	8.5	72	119.3
1027834	7 G 1.5	10.3	100.8	169.5
1027835	12 G 1.5	12.3	172.8	263.9
1027836	18 G 1.5	14.9	259.2	395.1
1027837	25 G 1.5	17.9	360	549.4
1027840	3 G 2.5	8.4	72	115.6
1027841	4 G 2.5	9.3	96	148.2

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03\_16



# ÖLFLEX® CHAIN 819 P

Article number	(CORE) / (mm <sup>2</sup> )	(mm)	(kg/km)	(kg/km)
1027844	5 G 2.5	10.4	120	186
1027842	7 G 2.5	12.7	168	268.9
1027843	12 G 2.5	15.2	288	420.2
1027850	4 G 4.0	11.1	153.6	222.1
1027852	4 G 10.0	17.2	384	541
1027855	4 G 16.0	20.1	614.4	804.6
1027857	4 G 25.0	24.9	960	1,259.5

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16