

# ÖLFLEX® CHAIN 90 CP

PUR

ÖLFLEX® CHAIN 90 CP - UL/cUL AWM

- 가



(24.04.2024)

# ÖLFLEX® CHAIN 90 CP



PUR 가 가 가  
, ,  
EMC 가 가  
  
가 가

- VDE 0472-815
  - IEC 60332-1-2 UL/cUL VW-1, FT1
  - IEC 60332-3-24 Cat. C /-25 Cat. D
- , UV

EMC-

DNV GL approved  
: UL AWM Style 11624, VW-1  
: cUL AWM I/II A, FT1  
UL File No. E63634  
: 가 T3

(class 6)  
: TPE  
, (RAL 9005 )

ETIM 5: ETIM 5.0 Class-ID: EC000057  
ETIM 5.0  
ETIM 6: ETIM 6.0 Class-ID: EC000057  
ETIM 6.0 Class :  
: 가

# ÖLFLEX® CHAIN 90 CP

:	VDE 0295 class 6, IEC 60228 class 6	가
:	: 7.5 x : 3 x	
:	IEC: U <sub>0</sub> /U 600/1000 V UL & CSA: 1000 V	
:	4000 V	
:	: -35°C ~ +80°C : -50°C +80°C	
:	A2-1	

www.lappkabel.de/en/cable-standradlengths ( : ) 가  
: 30 kg or 250 m,  
(e.g. 1 x 500 m or 5 x 100 m ).

가 VAT 가 가 .



# ÖLFLEX® CHAIN 90 CP

	(mm <sup>2</sup> )	(mm)	(kg/km)	(kg/km)
ÖLFLEX® CHAIN 90 CP				
1026547	1.5	7	23.8	60
1026548	2.5	7.6	41	90
1026549	4	7.9	58.8	100
1026550	6	8.4	81.3	120
1026551	10	9.8	123	180
1026553	16	11.3	187.7	240
1026555	25	13	280.6	340
1026557	35	14.2	398.9	480
1026559	50	16.8	551.7	610
1026561	70	19.1	773.2	880
1026563	95	21.6	1,036.6	1160
1026565	120	23.6	1,277.7	1380
1026567	150	25.9	1618	1670
1026569	185	28.5	1,957.3	1980
1026571	240	33.4	2,511.7	2600
1026573	300	35.3	3117	3210

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03\_16