

ÖLFLEX® CHAIN 809 SC CY

PVC PVC -

ÖLFLEX® CHAIN 809 SC CY - UL/cUL AWM

EMC AWM 가



가 , 가

(23.04.2024)

ÖLFLEX® CHAIN 809 SC CY

가

가

UL/CSA: VW-1, FT1.
IEC/EN: 60332-1-2
DIN EN 50290-2-22(TM54)

EMC-

VDE 0250 / 0285
UL-AWM-Style 10107
cRU AWM II A/B FT1
UL File No. E63634

: 가 T3

: PVC

PVC , (RAL 9005)

ETIM 5:

ETIM 5.0 Class-ID: EC000057
ETIM 5.0

ETIM 6:

ETIM 6.0 Class-ID: EC000057
ETIM 6.0 Class :

: , 가
: VDE 0295 5/ IEC 60228 5
가 가
: Flexing: up from 10 x outer diameter
: 4 x
: IEC: U₀/U 600/1000 V
UL & CSA: 600 V
: 4000 V
: : 0°C~+70°C(UL: +90°C)
Fixed installation: -40°C to +80°C
(UL: +90°C)

: A2-1

(:) 가

(23.04.2024)



ÖLFLEX® CHAIN 809 SC CY

www.lappkabel.de/en/cable-standradlengths
: 30 kg or 250 m,
(e.g. 1 x 500 m or 5 x 100 m).

가 VAT 가 가 .

(23.04.2024)



ÖLFLEX® CHAIN 809 SC CY

	(mm ²)	(mm)	(kg/km)	(kg/km)
ÖLFLEX® CHAIN 809 SC CY				
1062940	6	8.1	76	126
1062941	10	9.7	122	190
1062942	16	10.6	180	250
1062943	25	12	268	351
1062944	35	14.8	392	519
1062945	50	16.8	544	686
1062946	70	18.5	766	885
1062947	95	20.9	1020	1135
1062948	120	24.1	1272	1443
1062949	150	26.1	1593	1788
1062950	185	28.4	1941	2177
1062951	240	31.9	2518	2671
1062952	300	33.5	3116	3299

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16