

# ÖLFLEX® SERVO 2YSLCY-JB

EMC

ÖLFLEX® SERVO 2YSLCY-JB -

, EMV

EMC

3+3

CPR: [www.lappkabel.com/cpr](http://www.lappkabel.com/cpr)



EMC- , EN 61800-3

3+3

, 가

: IEC 60332-1-2

VDE 0207 / 0250 / 0295

(01.05.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16

# ÖLFLEX® SERVO 2YSLCY-JB

: PE (3+3 )  
 : PVC 가  
 4 : PVC , -  
 3+3 : PVC , -

ETIM 5: ETIM 5.0 Class-ID: EC000057  
 ETIM 5.0  
 ETIM 6: ETIM 6.0 Class-ID: EC000057  
 ETIM 6.0 Class :  
 : HD 308 S2 VDE 0293-308  
 : VDE 0295 5/ IEC 60228 5  
 가 가  
 : : 15 x  
 : 4 x  
 : U0/U: 600/1000 V  
 : Core/Core: 4 kV  
 : Core/Screen: 4 kV  
 : G = GN-YE  
 : X =  
 : 3+3  
 : : -5°C ~ +70°C  
 3+3 : -15°C ~ +70°C  
 : -40°C +70°C

가 가 ( ) 가  
 : [www.lappkabel.de/en/cable-standradlengths](http://www.lappkabel.de/en/cable-standradlengths)  
 30 kg or 250 m,  
 . (e.g. 1 x 500 m or 5 x 100 m ).  
 가 VAT 가 가



ÖLFLEX® SERVO 2YSLCY-JB

Article number	(CORE) / (mm <sup>2</sup> )	(mm)	(kg/km)	(kg/km)
ÖLFLEX® SERVO 2YSLCY-JB / 4 -				
0036425	4 G 1.5	11.4	95	230
0036426	4 G 2.5	12.4	150	300
0036427	4 G 4.0	15.6	235	485
0036428	4 G 6.0	17	320	630
0036429	4 G 10.0	19.6	533	860
0036430	4 G 16.0	22.1	789	1290
0036431	4 G 25.0	26.3	1236	1860
0036432	4 G 35.0	29.5	1662	2610
0036433	4 G 50.0	35.8	2345	2950
0036434	4 G 70.0	40.3	3196	3950
0036435	4 G 95.0	46.5	4316	5300
0036436	4 G 120.0	53.2	5435	6600
0036437	4 G 150.0	57.3	6394	7590
0036438	4 G 185.0	62.3	7639	9420
ÖLFLEX® SERVO 2YSLCY-JB BK / 4 -				
1136450	4 G 1.5	11.4	95	230
1136451	4 G 2.5	12.4	150	300
1136452	4 G 4.0	15.6	235	485
1136453	4 G 6.0	17	320	630
1136454	4 G 10.0	19.6	533	860
1136455	4 G 16.0	22.1	789	1290
1136456	4 G 25.0	26.3	1236	1860
1136457	4 G 35.0	29.5	1662	2610
1136458	4 G 50.0	35.8	2345	2950
1136459	4 G 70.0	40.3	3196	3950
1136460	4 G 95.0	46.5	4316	5300
1136461	4 G 120.0	53.2	5435	6600
1136462	4 G 150.0	57.3	6394	7590
1136463	4 G 185.0	62.3	7639	9420
ÖLFLEX® SERVO 2YSLCYK-JB / 3+3 -				
0036439	3 X 1,5 + 3 G 0,25	11.4	88	140

(01.05.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03\_16



# ÖLFLEX® SERVO 2YSLCY-JB

Article number	(CORE) / (mm <sup>2</sup> )	(mm)	(kg/km)	(kg/km)
0036440	3 X 2,5 + 3 G 0,5	12.2	144	230
0036441	3 X 4 + 3 G 0,75	14.4	224	323
0036442	3 X 6 + 3 G 1,0	15.7	276	420
0036443	3 X 10 + 3 G 1,5	18	491	635
0036444	3 X 16 + 3 G 2,5	20.2	723	930
0036445	3 X 25 + 3 G 4	23.8	1136	1350
0036446	3 X 35 + 3 G 6	26.9	1535	1780
0036447	3 X 50 + 3 G 10	32.6	2156	2530
0036448	3 X 70 + 3 G 10	36.4	2871	3225
0036449	3 X 95 + 3 G 16	42	3953	4511
0036450	3 X 120 + 3 G 16	47.8	4836	5663
0036451	3 X 150 + 3 G 25	51.6	5412	6720
0036479	3 X 185 + 3 G 35	56.5	7041	7855
0036453	3 X 240 + 3 G 50	65.1	8986	9770

(01.05.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16