

ÖLFLEX® TRUCK 170 TWIN

ÖLFLEX® TRUCK 170 TWIN - PVC , , 60V DC, ADR, TÜV, ISO



) 가 . 가 (가 (. /)
ADR

- , , 가

ADR TÜ.EGG.091-04

: PVC
PVC-

ÖLFLEX® TRUCK 170 TWIN

ETIM 5: ETIM 5.0 Class-ID: EC001578
ETIM 5.0 Class 가

ETIM 6: ETIM 6.0 Class-ID: EC001578
ETIM 6.0 Class :
: 15 x
: 60 V DC
: 3000 V AC
: : -40°C ~ +85°C
: , Class A

가 가 . (.) 가 .
www.lappkabel.de/en/cable-standradlengths
: 30 kg or 250 m,
(e.g. 1 x 500 m or 5 x 100 m).
가 .
가 VAT 가 가 .



ÖLFLEX® TRUCK 170 TWIN

	(CORE) / (mm ²)	, x (mm)	(kg/km)
ÖLFLEX® TRUCK 170 TWIN PVC/PVC			
7027055	PVC/PVC 2 x 6,0	15.2 x 7.1	115.2
7027056	PVC/PVC 2 x 10,0	18.8 x 8.9	192
7027057	PVC/PVC 2 x 16,0	21 x 10	307.2
7027058	PVC/PVC 2 x 25,0	25.6 x 12.3	480
7027059	PVC/PVC 2 x 35,0	28.4 x 13.5	672
7027054	PVC/PVC 2 x 50,0	33 x 16	960

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16