

ÖLFLEX® TRUCK 470 P FLRYY11Y

ÖLFLEX® TRUCK 470 P FLRYY11Y -
PVC

, 60V DC, ADR, TÜV, ISO6722, ISO4141-3 PUR /

가



ADR ADR

가

UV-

가

(23.12.2023)

ÖLFLEX® TRUCK 470 P FLRYY11Y

ISO 4141 DIN/ISO 6722

: PVC
PVC

ETIM 5: ETIM 5.0 Class-ID: EC000104
ETIM 5.0

ETIM 6: ETIM 6.0 Class-ID: EC000104
ETIM 6.0 Class :

:
: ISO 4141-3 50 pF/m , 100pF/m

: DIN/ISO 6722

: 12 x

: 60 V

: 5 kV rms , 5 .

: : -40°C ~ +85°C
, Class A

가 가 . (.) 가 .
: www.lappkabel.de/en/cable-standradlengths
30 kg or 250 m,
(e.g. 1 x 500 m or 5 x 100 m).

가 VAT 가 가 .

(23.12.2023)

ÖLFLEX® TRUCK 470 P FLRYY11Y

Article number	(CORE) / (mm ²)	(mm)		(kg/km)	(kg/km)
ÖLFLEX® TRUCK 470 P FLRYY11Y					
7027080	2 x 1,0	6	-	19.2	55
7027081	2 x 1,0	6	-	19.2	55
7027020	2 x 1,5	6.6	-	28.8	68
7027021	2 x 1,5	6.6	-	28.8	68
7027082	3 x 1,0	6.3	- -	28.8	67
7027022	3 x 1,0	6.3	/ / , ISO	28.8	67
7027083	4 x 1,0	6.8	/ / /	38.4	81
7027084	5 x 1,0	7.5	/ / / /	48	97
7027085	5 x 1,0 + 1 x 2,5	9	1.0 = / / / / ; 2.5 =	72	133
7027025	5 x 1,0 + 1 x 2,5	9	1.0 = / / / / ; 2.5 = , ISO	72	133
7027130	7 x 0,75	7.3	/ / / / / /	50.4	101
7027088	7 x 1,5	8.9	/ / / / / /	100.8	166
7027089	8 x 1,5 + 1 x 2,5	11.7	ISO 4141 + /	139.2	239
7027090	10x1,5+3x2,5+1x(2x1,5)	14.4	가 ; 1.5 = no. 1 - 3, 5 - 8, 10 - 12; 2.5 = no. 4, 9, 13; 1.5 = no. 14, 15	244.8	391
7027030	10x1,5+3x2,5+1x(2x1,5)	14.4	ISO 12098	244.8	395
7027091	10x1,5+3x2,5	14.4	가 ; 1.5 = no. 1 - 3, 5 - 8, 10 - 12; 2.5 = no. 4, 9, 13	216	367
7027031	10x1,5+3x2,5	14.4	1.5 = / / / / / / / / - / - ; 2.5 = / / -	216	367
7027046	2 x 0,75 + 2 x 1,5	7.2	0.75 = - ; 1.5 = -	43.2	85
7027092	2 x 6 + 3 x 1,5 ABS	12.1	DIN 72570 6.0 = / ; 1.5 = / /	158.4	267
7027093	2x6+3x1,5+1x(2x1,5) EBS	12.1	DIN 72570 6.0 = / ; 1.5 = / / ; 1.5 = - / -	187.2	321

(23.12.2023)

©2023 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



ÖLFLEX® TRUCK 470 P FLRYYY11Y

Article number	(CORE) / (mm ²)	(mm)		(kg/km)	(kg/km)
7027094	2x4+3x1,5+1x(2x1,5) EBS	11.9	4.0= / ; 1.5= / / ; 1.5= / -	148.8	257
7027024	18 x 1,5	13.7	가	259.2	407
7027032	25 x 1,5	16.1	가	360	560

(23.12.2023)

©2023 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16