

## ÖLFLEX® CLASSIC 100 YELLOW

ÖLFLEX® CLASSIC 100 YELLOW -	PVC	,	,	, 450/750V,
YSLY YY				

CPR: www.lappkabel.com/cpr









4kV

• •

WTG( )

: IEC 60332-1-2

, T1

IEC 60227-5 EN 50525-2-51

(24.04.2024)

©2024 Lapp Group - all rights reserved. http://lappkorea.lappgroup.com data sheet PN 0456 / 02\_03.16



## ÖLFLEX® CLASSIC 100 YELLOW

가 PVC LAPP P8/1 (RAL 1016) PVC ETIM 5.0 Class-ID: EC001578 ETIM 5: ETIM 5.0 Class ETIM 6: ETIM 6.0 Class-ID: EC001578 ETIM 6.0 Class VDE 0293-308, Т9 IEC 60228/VDE 0295 class 5 WTG TW-0 & TW-1, : 15 x : 4 x U0/U: 450/750 VAC U0/U: 600/1000 V 4000 V G = GN/YEX = GN/YE: -5°C ~ +70°C : -40°C +80°C 가 ( . ) 가 www.lappkabel.de/en/cable-standradlengths 30 kg or 250 m, . (e.g. 1 x 500 m or 5 x 100 m ). 가 VAT 가 가 .

Article number	(CORE) / (mm²)	(mm)	(kg/km)	(kg/km)				
ÖLFLEX® CLASSIC 100 YELLOW; U0/U: 450/750 V								
0010400	3 G 1.5	8.1	43	95				
00104023	4 G 1.5	8.9	58	117				
00104033	5 G 1.5	10	72	144				
0010401	3 G 2.5	9.6	72	152				
00104043	4 G 2.5	10.7	96	205				
00104053	5 G 2.5	11.8	120	225				

## ÖLFLEX® CLASSIC 100 YELLOW