

SILVYN® LCC-2

SILVYN® LCC-2

PVC



가

PVC

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



SILVYN® LCC-2

:

ETIM 5:

ETIM 5.0 Class-ID: EC001179

ETIM 5.0 class :

ETIM 6:

ETIM 6.0 Class-ID: EC001179

ETIM 6.0 Class :

:

(RAL 9005), UV

:

: PVC

:

-15°C ~ +70°C

가 VAT 가 가 .

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



SILVYN® LCC-2

	()	ID x OD mm	(mm)	SILVYN® LGF-2-M/LGS-2-M	PU ring (m)
SILVYN® LCC-2					
61804702	10	6.8 x 10.0	25	M12x1,5	30
61804712	12	10.2 x 14	40	M16x1,5/1	30
61804722	16	13 x 17	45	M16x1,5/2 + M20x1,5/1	30
61804732	20	16.9 x 21.5	50	M20x1,5/2	30
61804742	25	21.1 x 26	60	M25x1,5	30
61804752	32	28.1 x 34	90	M32x1,5	30
61804762	40	37.6 x 44.5	120	M40x1,5	10
61804772	50	48.4 x 55	130	M50x1,5	10
61804792	63	57.5 x 64.5	160	M63x1,5	10
61804787	75	70 x 79	190	M75x1,5	10
61737351	10	6.8 x 10.0	25	M12x1,5	10
61737352	12	10.2 x 14.0	40	M16x1,5/1	10
61737353	16	13.0 x 17.0	45	M16x1,5/2 + M20x1,5/1	10
61737354	20	16.9 x 21.5	50	M20x1,5/2	10
61737355	25	21.1 x 26.0	60	M25x1,5	10
61737356	32	28.1 x 34.0	90	M32x1,5	10

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16