

SILVYN® LCW-M

SILVYN® LCW-M

(seal)

IP65



SILVYN® :
LCC-2 / LCCH-2

가

(26.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

SILVYN® LCW-M

90° 6

ETIM 5:

ETIM 5.0 Class-ID: EC001180

ETIM 5.0 Class :

ETIM 6:

ETIM 6.0 Class-ID: EC001180

ETIM 6.0 Class :

:

:

: PA ()

가:

IP 65

:

-50°C ~ +135°C

가 VAT 가 가 .

(26.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



SILVYN® LCW-M

		SW 1/2 mm	mm	(thread) (mm)	SILVYN® LCC-2/LCCH-2	/ PU
SILVYN® LCW-M						
55503234	16 x 1.5/1	20 / 24	31	10	12	10
55503235	16 x 1.5/2	20 / 26	31	10	16	10
55503230	20 x 1.5/1	24 / 26	36	13	16	10
55503231	20 x 1.5/2	24 / 29	37	13	20	10
55503232	25 x 1.5	30 / 35	44	14	25	10
55503233	32 x 1.5	36 / 42	53	15	32	2