

SILVYN® UI COMPACT M

SILVYN® UI COMPACT M - SILVYN® UI 511

Space-saving due to compact dimensions.



**CE UK
CA**



(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

SILVYN® UI COMPACT M

SILVYN® UI 511 :

6

ETIM 5:

ETIM 5.0 Class-ID: EC001180

ETIM 5.0 Class :

ETIM 6:

ETIM 6.0 Class-ID: EC001180

ETIM 6.0 Class :

:

AISI 304

DW no. 1.4301

가:

IP 40

:

-45°C to +105°C (with O-Ring)

-55°C to +260°C (without O-Ring)

가 VAT 가 가 .

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



SILVYN® UI COMPACT M

		(mm)	SILVYN® UI 511	/ PU
SILVYN® UI COMPACT M ()				
61803880	16 x 1.5	9.8	3/8"	1
61803881	20 x 1.5/1	9.8	3/8"	1
61803882	20 x 1.5/2	13.9	1/2"	1
61803883	25 x 1.5	18.5	3/4"	1
61803884	32 x 1.5	22.8	1"	1
61803885	40 x 1.5	30.8	1 1/4"	1
61803886	50 x 1.5	36.8	1 1/2"	1
61803887	63 x 1.5	47.8	2"	1
SILVYN® UI COMPACT M ()				
61803870	16 x 1.5/1	6.8	5/16"	1
61803871	16 x 1.5/2	9.8	3/8"	1
61803872	20 x 1.5/1	6.8	5/16"	1
61803873	20 x 1.5/2	9.8	3/8"	1
61803874	20 x 1.5/3	13.9	1/2"	1
61803875	25 x 1.5	18.5	3/4"	1
61803876	32 x 1.5	22.8	1"	1
61803877	40 x 1.5	30.8	1 1/4"	1
61803878	50 x 1.5	36.9	1 1/2"	1
61803879	63 x 1.5	47.9	2"	1