

SILVYN® EC

SILVYN® EC -



가

SILVYN® FPAS :

ETIM 5:

ETIM 5.0 Class-ID: EC000519

ETIM 5.0 Class :

ETIM 6:

ETIM 6.0 Class-ID: EC000519

ETIM 6.0 Class :

:

FPAS67 SILVYN® REC

:

(RAL 9005), UV

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



SILVYN® EC

:

NEC: PA66

REC: TPE

:

NEC: -50°C ~ +135°C REC: -50°C ~ +120°C

가 VAT 가 가 .

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



SILVYN® EC

	()	Clamping range in mm	(mm)	SILVYN® FPAS	/ PU
SILVYN® NEC					
55507097	16	-	10.5	16	10
55507098	21	-	15	21	10
55507099	28	-	20	28	10
55507100	34	-	25.5	34	10
55507101	42	-	32	42	10
55507102	54	-	43.5	54	10
SILVYN® REC					
55507040	10	3 - 7	-	10	10
55507041	13	3 - 7	-	13	10
55507042	16	3 - 11	-	16	10
55507043	21	3 - 15	-	21	10
55507044	28	3 - 21	-	28	10
55507045	34	3 - 25	-	34	10
55507046	42	5 - 34	-	42	10
55507047	54	5 - 46	-	54	10



SILVYN® EC



(24.04.2024)

©2024 Lapp Group - all rights reserved.
<http://lappkorea.lappgroup.com>
data sheet

PN 0456 / 02_03.16